


REV	DOCUMENT	CHANGED BY	CHECK
8	0081848	NMN 19SEP11	CMH



RELEASE NO: SR-7230

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:		DRAWN		O.M.W		15JAN58		Honeywell							
OPERATING FORCE----- 9-13 OZ		CONTACT ARRANGEMENT S P D T				CHECK		GCH		28JAN58									
RELEASE FORCE----- 4 OZ MIN		15A-125, 250 OR 480 VAC, 2A-600 VAC -L74- 1/8 HP - 125 VAC; 1/4 HP - 250 VAC 1/2A - 125 VDC; 1/4A-250 VDC CE 1.5A, 240VACUL		NO PLACES X ± .030		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.						TITLE SWITCH - ENCLOSED							
DIFFERENTIAL TRAVEL----- .002 MAX				ONE PLACE .X ± .015															
OVERTRAVEL----- .140 MIN				THREE PLACE .XXX ± .005		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY													
SWITC-BASIC REPLACEMENT----- BZ-2RQ69		ANGLES X ± 0°		THIRD ANGLE PROJECTION 															
										RASTER						SIZE		TYPE	
										B		I		-		BZV6-2RQ9		8	
										SCALE		NONE		WEIGHT .58 LB		SHEET 1		OF 1	