







PARAMETER	MIN	TYP	MAX	UNITS	CONDITIONS/REMARKS
SUPPLY VOLTAGE	6.6	8.0	12.6	VOLTS	-40°C TO +125°C
SUPPLY CURRENT		13	30	mA	MAX @ 12.6 V @ -40°C
OUTPUT CURRENT			1	mA	SINKING OR SOURCING
OUTPUT SPAN		.625 V _S		VOLTS	-500G TO +500G @ 25°C /5\
SENSITIVITY	4.90	5.0	5.10	mV/g	@ 8.0 V _S & 25°C
LINEARITY	-1.5	-.8	0.0	% OF SPAN	DEV FROM STR LINE THRU -500 AND +500
V _{OUT} @ 0 GAUSS	3.960	4.000	4.040	VOLTS	25°C
TEMP ERROR-NULL	-.02		+.02	%/°C	-40°C TO +125°C
TEMP ERROR-GAIN	-.02		+.02	%/°C	-40°C TO +125°C

BLOCK DIAGRAM CURRENT SINKING OR SOURCING OUTPUT



- NOTES
- 1 CENTERLINE OF HALL CELL (IC) ONLY. THE LOCATION OF THE CERAMIC COVER IS NOT SPECIFIED
- 2 THE + MAGNETIC FLUX IS IN THIS DIRECTION (THIS ASSUMES THE CONVENTION THAT THE DIRECTION OF THE EXTERNAL FLUX OF A MAGNET IS FROM THE NORTH TO THE SOUTH POLE OF THE MAGNET)
- 3 - THE DEVICE CANNOT BE DAMAGED BY MAGNETIC OVERDRIVE
- 4 - OUTPUT TYPE - RATIOMETRIC
- 5 THE OUTPUT IS CLAMPED AT 9.0 VDC MINIMUM, 9.5 VDC TYPICAL
- 6 ARTWORK TYPICAL

THIRD ANGLE PROJECTION



SCALE 5 : 1

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE	(.0)	$\pm .030$
-----------	------	------------

TWO PLACE	(.00)	+.015
-----------	-------	-------

TWO PLACE	(1.007) $\pm$ 0.019
THREE PLACE	(1.000) $\pm$ 0.005

THREE PLACE (.000) $\pm .005$
ANGLE

ANGLES	$\pm$
--------	-------

WEIGHT

WEIGHT

