


Part Number : 10844150
Product Description : 6.35mm Pitch MLX Power Connector Header, Vertical, 15 Circuits, PA Polyamide Nylon 6/6 94V-2, Tin (Sn) Plating, White
Series Number : 42002
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Part Number : A-42002-15A1A1

Documents and Resources

Drawings

010844150_sd.pdf

PK-43255-001-001.pdf

PK-43255-003-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

PSX-42002-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	42002
Description	6.35mm Pitch MLX Power Connector Header, Vertical, 15 Circuits, PA Polyamide Nylon 6/6 94V-2, Tin (Sn) Plating, White
Application	Wire-to-Board
Comments	Solder Type
Component Type	PCB Header
Product Name	MLX
UPC	800753619876

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	13.5A, 20.0A

Physical

Breakaway	No
Circuits (Loaded)	15

Downloaded from Arrow.com.

Circuits (maximum)	15
Color - Resin	Natural
Durability (mating cycles max)	50
First Mate / Last Break	No
Gender	Male
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Mounting Style	Through Hole
Net Weight	7.726/g
Number of Rows	3
Orientation	Vertical
Packaging Type	Bag
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	4.27mm
Pitch - Mating Interface	6.35mm
Pitch - Termination Interface	6.35mm
Plating min - Mating	3.500µm
Plating min - Termination	3.560µm
Polarized to PCB	Yes
Shrouded	Shrouded
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	WAVE
Max-Temp	260

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.13mm Diameter MLX Power Crimp Housing Plugs	42021

Downloaded from Arrow.com.