Part Number : 2191160161
Product Description : Micro-Fit+ PCIe CEM5 Right-Angle Header, Through Hole, 3.00mm Pitch, 3 Rows, 16 Circuits (12 Power, 4 Signal), Matte Tin (Sn) Plating, Black, Tray
Series Number : 219116
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2191160161_sd.pdf

2191160161-PK.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2191160001-AS-000.pdf

2191160001-PS-000.pdf

2191160001-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	219116
Description	Micro-Fit+ PCIe CEM5 Right-Angle Header, Through Hole, 3.00mm Pitch, 3 Rows, 16 Circuits (12 Power, 4 Signal), Matte Tin (Sn) Plating, Black, Tray
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Micro-Fit+ PCIe
UPC	196823270406

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	9.2A (Power), 1.0A (Signal)
Voltage - Maximum	600V AC (RMS)/DC

Physical

Downloaded from Arrow.com.

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	Yes
Flammability	94V-0
Gender	Male
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer (LCP)
Mounting Style	Through Hole
Net Weight	2.105/g
Number of Rows	3
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	3.18mm
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
(p)ower-(s)ignal Configuration	12p - 4s
Shrouded	Shrouded
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit+ PCIe CEM5 Dual Row Receptacle Housings	219114

Downloaded from Arrow.com.