

4

3

2

1






used for:

D-SUB HD

Part NO.	POS.	A -0.76	B -0.25	C	D ± 0.13	E ± 0.13	F ± 0.13	G ± 0.13	H ± 0.13
302A10129X	15	31.19	16.46	25.00 $^{+0.12}_{-0.13}$	20.5	22.2	25.00	11.4	13.0
302A10139X	26	39.52	24.79	33.30 $^{+0.15}_{-0.1}$	28.8	30.5	33.30	11.4	13.0
302A10149X	44	53.42	38.50	47.04 ± 0.13	42.5	44.3	47.04	11.4	13.0
302A10159X	62	69.70	54.96	63.50 ± 0.13	59.1	60.7	63.50	11.4	13.0

(b)

(b) RECOMMENDED PANEL CUT-OUT



APPROVAL * FREIGABE * DEBLOCKAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCKAGE * AUTOR/ZACON * APPROVAL	


RoHS compliant

NOTES:

- (c) 1. METAL SHELLS: STEEL; NICKEL PLATED
 2. INSULATORS: PBT GF UL 94 V-0, BLACK
 3. CONTACTS: COPPER ALLOY
 PLATING: GOLD FLASH over NICKEL
 SOLDER CUP ACCEPTS CABLE AWG 22
 4. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR
 REPRODUCED IN ANY WAY, AND MAY NOT
 BE PASSED ON TO A THIRD PARTY WITHOUT
 WRITTEN PERMISSION.
 OWNERSHIP AND COPYRIGHT OF CONEC GmbH
 DO NOT ALTER CAD DRAWING BY HAND

				tolerance		
				2002	date	name
				drawn	11.10.	Parei
				appd.	11.10.	Mickenbecker
				norm	DIN 41652	
1 x c	Ä19-0067	24.07.2019	JLE	d-old		
2 x b	Ä6008	03.06.2014	Lehmen.			
a	Original					
rev.	description	date	name			



scale: 2:1
 material: SEE NOTES

title:
 D-SUB HD FEMALE
 15-62pos. SOLDER CUP

dwg no: AutoCAD 2000 DIN-A
 16K1A782 4
 sh: 1/1
 part no: SEE TABLE

4

3

2

1