

## Dual-Port USB Wall Charger with PD Charging - USB-C (39W) & USB-A (5V 2.4A/12W)

MODEL NUMBER: U280-W02-A1C1



Dual USB wall charger quickly charges a USB-C device and a USB-A device, including tablets and smartphones, at the same time.

### Features

**Dual USB Wall Charger Charges 2 Mobile Devices Simultaneously** This dual-port USB wall charger with Quick Charge 2.0 technology lets you quickly and safely charge one USB-C mobile device and USB-A mobile device at the same time. Plug into any NEMA 1-15R, NEMA 5-15R or NEMA 5-15/20R outlet to ensure your smartphones, tablets and MP3 players, to name just a few devices, receive a satisfactory battery charge. The dual USB wall charger is compatible with Apple, Android, Windows and Amazon devices with USB-C, Thunderbolt 3 or USB-A charging ports.

**USB-C PD Charging Port Supports Quick Charge 2.0 Technology** The USB-C port is PD 2.0 compatible, supporting Quick Charge 2.0 Class A 5/9/12V technology. Instead of charging at a preset power level, this dual-port USB wall charger adapter adjusts to provide as much power as your QC-compliant device's battery can handle. Available outputs include 5V/3A (15W), 9V/3A (27W) and 15V/2.6A (39W), which can charge your QC 2.0 device much faster than traditional chargers.

**Built-In Auto-Sensing Adjusts to Proper Power Level** The USB-A port features auto-sensing technology that detects the connected device and automatically adjusts to the appropriate power level up to 5V 2.4A, perfect for fast-charging tablets and e-readers.

**Folding Plug Design Perfectly Sized for Travel** The dual USB travel charger is easy to carry in your purse, suitcase, backpack or laptop bag. The NEMA 1-15P plug folds into the unit when not in use to shield it from damage and prevent it from snagging or scratching your bag's contents.

## Specifications

OVERVIEW	
UPC Code	037332214416
Product Type	Wall Charger
Charging Form Factor	Direct Plug-In

### Highlights

- Ideal for charging smartphones, tablets, e-readers and MP3 players while traveling
- USB-C PD Charging port supports Quick Charge 2.0 Class A 5/9/12V technology
- Auto-sensing USB-A port adjusts charging power level to your device up to 5V 2.4A
- Maximum charging power output of 51W: 39W USB-C and 12W USB-A
- Plug folds inward to protect it from damage and help the unit fit into a purse or bag

### Applications

- Charge up to 2 smartphones, tablets, cameras, e-readers or any other USB-C, Thunderbolt 3 or USB-A devices

### Package Includes

- U280-W02-A1C1 Dual-Port USB Wall Charger with PD Charging

Device Compatibility	Phone; Tablet; Amazon Kindle; Laptop; Chromebook
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Input Connection Type	NEMA 1-15P
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 1-15P (NON-POLARIZED)
Input Current	1.5A
<b>OUTPUT</b>	
Overload Protection	Yes
<b>CHARGING</b>	
Number of Charging Ports	2
Total Charging Amps	1.5A
Total Charging Watts	51
Charging Method	USB
Charging Port Type	USB A (FEMALE); USB C (FEMALE)
Charging Ports Details	USB-C: 39WUSB-A: 5V 2.5A (12W)
Charging Ports / Amps	(1) 2.4A; (1) 3A / 2.6A
Charging Method Detail	Power Deliver 2.0; Quick Charge 2.0
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	1.46 x 5.51 x 5.35
Shipping Dimensions (hwd / cm)	3.71 x 14.00 x 13.59
Shipping Weight (lbs.)	0.41
Shipping Weight (kg)	0.19
Unit Dimensions (hwd / in.)	2.900 x 2.500 x 1.200
Unit Dimensions (hwd / cm)	7.5 x 6.3 x 3
Unit Packaging Type	Box
Unit Weight (lbs.)	0.30
Unit Weight (kg)	0.14
<b>ENVIRONMENTAL</b>	

Operating Temperature Range	32° to 95°F (0° to 35°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Operating Humidity Range	30 TO 90% RH, Non-Condensing
Storage Humidity Range	10 TO 90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Number of Ports	2
Side A - Connector 1	NEMA 1-15P (NON-POLARIZED)
Side B - Connector 1	USB A (FEMALE); USB C (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Quick Charge Compliant	No
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL Listed
Product Compliance	RoHS; REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty