



Part Number : [5013340100](#)

Product Description : 1.00mm Pitch, Pico-Clasp
Female Crimp Terminal, Tin Plating, 32-28 AWG, Bag

Series Number : 501334

Status : Not Recommended For New Design

Product Category : Crimp Terminals

Engineering Part Number : NT501-6746

Packaging Alternative : [5013340000](#) (Reel)



Documents and Resources

Specifications

[5013300000-AS-000.pdf](#)

[5013300000-AS-001.pdf](#)

[SPK-501334-001-001.pdf](#)

[5013300000-PS-001.pdf](#)

[5013301000-PS-001.pdf](#)

[5013301000-PS-003.pdf](#)

[PS-501331-001-001.pdf](#)

[5019390000-PS-002.pdf](#)

[5019391000-PS-002.pdf](#)

[5019401001-PS-001.pdf](#)

[5019401001-PS-CHI-001.pdf](#)

[5019401001-PS-JAP-001.pdf](#)

[5019401001-PS-KOR-001.pdf](#)

[5019401001-PS-SPA-001.pdf](#)

[PS-501940-001-001.pdf](#)

Tooling Specifications

[CS-501193-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
------------	-----------------------------

China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Crimp Terminals
Series	501334
Description	1.00mm Pitch, Pico-Clasp Female Crimp Terminal, Tin Plating, 32-28 AWG, Bag
Application	Signal, Wire-to-Board
Product Name	Pico-Clasp
UPC	822348531097

Electrical

Current - Maximum per Contact	2.0A
-------------------------------	------

Voltage - Maximum	100V AC (RMS)/DC
-------------------	------------------

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	8.600/mg
Packaging Type	Bag
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.80mm max.
Wire Size (AWG)	28, 30, 32
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Pico-Clasp Low-Halogen Single Row Receptacle Housings	<u>501330</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Pico-Clasp Wire-to-Board Terminals, 32-28 AWG	<u>638131700</u>
Hand Crimp Tool for 1.00mm Wire-to-Board Crimp Terminal, 32-28 AWG Wire	<u>638191500</u>

Japan

Description	Part Number
-------------	-------------

Crimp Hand Tool - Straight Action	<u>5780165300</u>
Hand Extraction Tool	<u>5780166000</u>

This document was generated on May 09, 2026