

4

3

2

1

© -TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

-----CONTINUATION OF SHEET 1

7

LOT CODE MARKING

1558A1

SPACEINTERNAL CONTROL No. (2-digit)

YEAR OF PRODUCTION WITH 1-DIGIT FIGURE(4TH DIGIT OF CALENDAR YEAR)
(EXAMPLE: Y2018: 8; Y2019: 9)

MONTH OF PRODUCTION WITH 1-DIGIT FIGURE OR ALPHABET
(EXAMPLE: 1~9, X(10), Y(11), Z(12))

DATE OF PRODUCTION WITH 2-DIGIT FIGURES(01-31)

8

MARK ALCO PLUS FIRST 5 DIGITS PER T&B P/N.2 AND 3 POSITION
SUPPLIED WITHOUT ALCO

ADF12T04	32.51[1.280]	YES	12	2-1825002-0
ADF1204	32.51[1.280]	NO	12	1-1825002-9
ADF10T04	27.40[1.078]	YES	10	1-1825002-8
ADF1004	27.40[1.078]	NO	10	1-1825002-7
ADF09T04	24.84[.978]	YES	9	1-1825002-6
ADF0904	24.84[.978]	NO	9	1-1825002-5
ADF08T04	22.30[.878]	YES	8	1-1825002-4
ADF0804	22.30[.878]	NO	8	1-1825002-3
ADF07T04	19.80[.778]	YES	7	1-1825002-2
ADF0704	19.80[.778]	NO	7	1-1825002-1
ADF06T04	17.22[.678]	YES	6	1-1825002-0
ADF0604	17.22[.678]	NO	6	1825002-9
ADF05T04	14.70[.578]	YES	5	1825002-8
ADF0504	14.70[.578]	NO	5	1825002-7
ADF04T04	12.14[.478]	YES	4	1825002-6
ADF0404	12.14[.478]	NO	4	1825002-5
ADF03T04	9.60[.378]	YES	3	1825002-4
ADF0304	9.60[.378]	NO	3	1825002-3
ADF02T04	7.06[.278]	YES	2	1825002-2
ADF0204	7.06[.278]	NO	2	1825002-1
T&B P/N	DIM L	SEAL	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.30[.012]

4 PLC ± -

ANGLES ± -

MATERIAL -

FINISH -

WEIGHT

CUSTOMER DRAWING

DWN
B.S.VISWESWARA

CHK
M.SARVER

APVD
M.SARVER

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT

19AUG03

TE Connectivity

DIP SWITCH, ADF THRU HOLE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1825002

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
1:1

SHEET
2 of 2

REV
R

1825002

B

A

1471-9 (1/15)

Downloaded from Arrow.com