

200mA, 35V Schottky Barrier Diode

FEATURES

- Designed for mounting on small surface
- Low Capacitance
- Low forward voltage drop
- Compliant to RoHS directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Adapters
- For switching power supply
- Low stored charge
- Inverter

MECHANICAL DATA

- Case:0603
- Molding compound meets UL 94 V-0 flammability rating
- Moisture sensitivity level: level 1, per J-STD-020
- Packing code with suffix "G" means green compound (halogen-free)
- Terminal: Matte Au plated leads, solderable per J-STD-002
- Meet JESD 201 class 1A whisker test
- Polarity: Indicated by cathode band
- Weight: 3 mg (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
$I_{F(AV)}$	200	mA
V_{RRM}	35	V
I_{FSM}	1.0	A
V_F at $I_F=200mA$	0.6	V
$T_{J\ MAX}$	125	°C
Package	0603	
Configuration	Single dice	



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)			
PARAMETER	SYMBOL	TSS0230U	UNIT
Marking code on the device		BB	
Repetitive peak reverse voltage	V_{RRM}	35	V
Forward current	$I_{F(AV)}$	200	mA
Peak Forward Surge Current 8.3 ms Single Half Sine-Wave Superimposed on Rate Load	I_{FSM}	1	A
Junction temperature range	T_J	-40 to +125	°C
Storage temperature range	T_{STG}	-40 to +125	°C

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode ⁽¹⁾	$I_F = 200\text{mA}$, $T_J = 25^\circ\text{C}$	V_F	-	0.6	V
Reverse current @ rated V_R per diode ⁽²⁾	$V_R = 10\text{V}$, $T_J = 25^\circ\text{C}$	I_R	-	1	μA
Junction capacitance	1 MHz, $V_R = 1\text{V}$	C_J	-	18	pF

Notes:

1. Pulse test with $PW = 0.3\text{ ms}$
2. Pulse test with $PW = 30\text{ ms}$

ORDERING INFORMATION

PART NO.	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING
TSS0230U (Note 1)	RG	G	0603	4K / 7" Reel

Notes:

1. Whole series with green compound

EXAMPLE

EXAMPLE P/N	PART NO.	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION
TSS0230U RGG	TSS0230U	RG	G	Green compound

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Characteristics




Fig.2 Reverse characteristics




Fig.3 Capacitance between terminals characteristics





Fig.4 Current derating curve



CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.5 VF Dispersion Map




Fig.6 IR Dispersion Map






Fig.7 CT Dispersion Map



PACKAGE OUTLINE DIMENSION



DIM.	Unit(mm)			Unit(inch)		
	Min	Typ	Max	Min	Typ	Max
L	1.60	-	1.80	0.063	-	0.071
W	0.80	-	1.00	0.031	-	0.039
T	0.70	-	0.85	0.028	-	0.033
C	-	0.45	-	-	0.018	-
D	-	0.70	-	-	0.028	-

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.