



Part Number : [1200668501](#)

Product Description : Micro-Change (M12) Double-Ended Cordset, 5 Poles, A-Coded, Male (Straight) to Female (Straight), 0.34mm² Black PUR LSOH Cable, 5.0m (16.40') Length

Series Number : 120066

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 885030H09M050




Documents and Resources

Drawings

[1200668501_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; 6,6'-Di-tert-butyl-2,2'-methylenedi-p-cresol per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120066
Description	Micro-Change (M12) Double-Ended Cordset, 5 Poles, A-Coded, Male (Straight) to Female (Straight), 0.34mm ² Black PUR LSOH Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78172541402

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	5.80mm (.230")
Cable Length	5.0m (16.40')

Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	207.800/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 21198
Wire Size (AWG)	22

This document was generated on Apr 20, 2026