



HONEYWELL PART NUMBER
4SX36-T
PRODUCT CODE VDF0960
FAA-PMA 

REV	DOCUMENT	CHANGED BY	CHECK
10	0038447	SS 28MAR08	BLR



- NOTES**
-  MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
 - 2- TERMINALS ARE PLATED FOR SOLDERING
 - 3- SWITCH WILL WITHSTAND TEMPERATURE OF 400°F
 - 4- SWITCH HAS A GREATER OVERTRAVEL THAN STANDARD CONSTRUCTION
ADDITIONAL OVERTRAVEL WILL TEND TO REDUCE MECHANICAL LIFE
 -  FOR MANUFACTURING DETAIL SEE ASSEMBLY DRAWING 4SX36-T FOR FAA-PMA

RELEASE NO. PR-253

REPLACES

CHARACTERISTICS	ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 			DRAWN	SPK	06FEB08	Honeywell			
OPERATING FORCE — — — 5 OZ MAX	CONTACT ARRANGEMENT SPDT						CHECK	RJ	06FEB08				
RELEASE FORCE— — — — 1 OZ MIN							0.030 0.015 0.005 THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC			
DIFFERENTIAL TRAVEL— — — .005 MAX													
OVERTRAVEL — — — — — .010 MIN				APPROVALS	KEMA, CE	7A 250V~ T125 5E4 				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE
	UL, CSA	7A 250 VAC 	BRAND L7	B	I	4SX36-T		10					
	AVIATION	FAA-PMA	BRAND	SCALE	-	WEIGHT:.003 LB MAX	SHEET 1 OF 1						