




CORE DIMENSIONS 40T0711-00H

UNCOATED CORE					
	MM	INCHES		MM	INCHES
OD	18.00	(.709)	±	.58	(.023)
ID	10.00	(.394)	±	.58	(.023)
TH	7.00	(.276)	±	.18	(.007)
EPOXY COATING					
OD	18.15	(.715)	±	.74	(.029)
ID	9.85	(.388)	±	.74	(.029)
TH	7.15	(.282)	±	.33	(.013)

WEIGHT / K 6.0036 KGS 13.2355 LBS
INITIAL PERMEABILITY 10000

ROOM TEMPERATURE ELECTRICAL SPECIFICATION									
	MIN. TOL.	MIN. (μH)	NOM. (μH)	MAX. (μH)	MAX. TOL.	FREQ. (kHz)	VOLT. (mV)	GAUSS	TURNS
L1-1T	-30.0%	5.76	8.23	10.70	30.0%	100	12.08	10	1
L2-10T	-30.0%	576.0	822.9	1069.8	30.0%	100	120.8	10	10
Q		4				100	12.08	10	1

COATING SPECIFICATIONS			
TYPE	Max. Coating (mm / mils.)	Min. DLB VAC	TEST FORCE (LB)
Epoxy	(0.1524 / 6.0)	1000	2.73

NOTES:



Rev	Description	Date	INT
A	Original Draft	1/24/2005	TPM
B	Revised template	5/26/2006	WMM
C	Revised template	2013-8-28	Jcai

Date: 2013-8-28	DWG # 40T0711-00H-C	Rev: C
Drawn By: Jcai	Title # 40T0711-00H	

Steward This document contains information which is proprietary to Steward. No production or publication of this document in whole or in part shall be made without written authorization from Steward.

UNCONTROLLED DOCUMENT