

PRODUCT NUMBER

10021507–104TRLF

- PLATING
  - 1 = 0.76µm GOLD/GXT ON CONTACT AREA
    2.0µm MIN MATTE TIN ON TAILS
  - 1.27µm Ni MIN UNDERPLATING
- TOTAL NUMBER OF POS
- PACKAGING SEE NOTE 3
- RoHS COMPATIBLE, SEE NOTE 5





RECOMMENDED PAD LAYOUT

NOTES:

1 – HOUSING MATERIAL : LCP

2 – TERMINAL MATERIAL : PHOSPHORE BRONZE

3 – PACKAGING TR = TAPE & REEL
(SEE TA845 FOR PACKAGING SPECS)

4 – HOLE DIMENSION TO BE : Ø1.95±0.07
FOR NON INTERFERENCE FIT (LOCATIONAL)
APPLICATIONS

5 – RoHS COMPATIBLE PRODUCT SPECIFICATIONS


a – PLATING:
– "LF" MEANS THE PRODUCT IS LEAD–FREE,


b – MANUFACTURING PROCESS COMPATIBILITY
– THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDS MAX IN A CONVECTION, INFRA–RED OR VAPOR PHASE OR REFLOW OVEN.

c – LABELLING:
– MEETS PACKAGING SPECS AS PER GS–14–920


d – LEGAL STATEMENT : SEE GS–47–0004

6 – CUSTOMER PART NUMBER : 99304882





SECTION A–A



mat'l. code				surface		tolerance		projection	product family
SEE NOTES				ISO 1302 ✓		ISO 406 ISO 1101			MINITEK
ltr	ecn no	dr	date	tolerances unless otherwise specified					title
A	F05–0414	LMU	05.12.14	angles	linear				UNKEYED MINITEK SI
B	F12–0031	JCO	12.03.20					mm	
C	B–16900	JCO	14.02.03					scale N/A	
D	B–19190	LMU	14.10.24	dr	L.MULIN	05.12.14			dwg no sheet 1 of 1
E	F–27876	LMU	17.08.31	engr	J.COMPAGNON	05.12.14		Amphenol FCi	10021507
F	F–28101	LMU	17.10.06	chr	---	---			type CUSTOMER Draw
				appd	JM.C	05.12.14			

sheet	revision
index	sheet

Amphenol FCi FCIconnect.com
Copyright FCI
Downloaded from Arrow.com.