

2CPSC1A3

[Products](#) > [Switches](#) > [Safety Switches](#) > [Cable-Pull Switches](#) > [2CPS Series](#) > **2CPSC1A3**

Overview

MICRO SWITCH 2CPS Series Cable Pull Safety Switch, Cable, Maintained Right Side, No Actuation Left Side, 2NC/2NO Direct Opening (Switch 2, Left: 1NC/1NO; Switch 2, Right: 1NC/1NO) [View More](#)



Technical Specifications

Product Type	Cable Pull Safety Switch	Actuator	Cable, Maintained Right Side, No Actuation Left Side
Switch Type	2NC/2NO Direct Opening (Switch 1, Left: 1NC/1NO; Switch 2, Right: 1NC/1NO)	Contact Material	Gold-plated
Cable Length	N/A	Termination Type	20 mm
Ampere Rating	10 uA to 50 mA Low Energy	Voltage	250 Vac and 60 Vdc max.
Housing Material	Zinc Die-Cast	Series Name	2CPS

[View More](#)

View documents in:

English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 CPS Series Cable Pull Safety Switch Datasheet	Datasheet	English	2MB
 PK 80155: 2 CPS Series Cable Pull Safety Switch	Installation Instructions and Approvals Documentation	English	1MB
 PK 80169: 2CPS Series Cable Pull Switch Without Broken Cable Detection	Installation Instructions and Approvals Documentation	English	538KB
 PK 80170: CPS-BRACKET Mounting Bracket, Issue 3 (Multiple Languages)	Installation Instructions and Approvals Documentation	English	519KB

[View More](#)

Product Features

- Positive opening operation of normally closed contacts
- Choice of 2NC/2NO or 3NC/1NO contact configurations

 view all 2CPSC1A3 literature

 view distributor inventory

 sample request

 email support

 get support

 email sales

 find a distributor

 email this page

- Maximum cable length in a single direction is 76 m (250 ft) for a combined length of 152 m (500 ft) in dual directions
- Choice of three actuator configurations
- Removable contact block version available
- Large wiring cavity with straight-through wiring
- 24 Vdc or 120 Vac bright, multi-cluster LED status indicator light available
- Gold-plated contacts are standard
- Die-cast zinc housing
- Optional hardware packs available
- UL, CE, CSA, SIL 3 capable

Applications

- Long conveyor systems found in warehouses and distribution centers
- Conveyor systems having a high amount of vibration
- Conveyor systems that experience wide temperature swings
- Long conveyor systems where easy through wiring, or highly visible trip status is required
- Perimeter guarding where hosedown conditions are present

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL INTERNATIONAL INC.