



ASSEMBLY NUMBER	PT NO. REF	SHELL	COUPLING	WASHER (2 REQD)	THREADED RING	END BELL
71-453314-	08P-10-	10-150924-103	10-123016-93	10-123015-10	10-150912-103	10-453103-10

48536-405		REVISIONS		
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	A1			
	B	(CL II) ADDED 10-252810-() ECN: A5160	7-7-08	H.BROOKER



ACCESSORIES
(NOT PART OF STANDARD ASSEMBLY)
SEE DRAWING. 10-150000

- DISTANCE BETWEEN END OF SHELL & THE POINT AT WHICH A GAGE PIN HAVING THE SAME BASIC DIA AS THE MATING CONTACT & A SQUARE FACE ENGAGES SOCKET CONTACT SPRING.
- FOR MATING RECEPTACLE ASSY, SEE DRAWING 71-149010-() & OTHERS.
- SEE WORK ORDER FOR PERMISSIBLE ADDITIONAL OR ALTERNATE STAMPING.
- INSERTS & CONTACTS MUST NOT BE REMOVED.
- FOR CONTACT ARRANGEMENTS & COAXIAL CONTACT DATA, SEE DRAWING L-15210-().
- UNITS ILLUSTRATED MEET THE MATERIAL & FINISH REQUIREMENTS OF MIL-C-26482.
- TO COMPLETE ASSEMBLY NO. & PT NO. REF, ADD APPLICABLE INSERT ARRANGEMENT SUFFIX TO BASE NUMBERS LISTED ABOVE PER 9-2437-1.
- FOR QUANTITIES & PART NUMBERS OF THE COMPONENTS FOR THE DESIRED UNIT SEE SEPARATE PARTS LIST.

NOTES:	NEXT ASSEMBLY
--------	---------------

SOLDER WELL DATA			
CONTACT SIZE	20	16	
WELL DIA	.046 ^{+.004} _{-.000}	.078 ^{+.004} _{-.002}	
WELL DEPTH	.031 ^{+.031} _{-.000}	.125	.188
COAXIAL DATA SEE NOTE 1			
FIND NO.	QTY REQD	CODE IDENT	PART NUMBER
DESCRIPTION			
NOTE REF			
PARTS LIST			
UNLESS OTHERWISE SPECIFIED		SIGNATURES	
LINEAR DIMENSIONS ARE IN INCHES. TOLERANCES: .XXX ± .010, .XX ± .03, .X ± .1, ANGLES ± 2°. OTHER STANDARDS PER 9-3800 AND MIL-D-1000. NOTE REF		DATES	
MATERIAL SPEC		PREPARED A. FLYZIK 7-22-68	
PROCESS SPEC TEST 9-3980-2 ASSY 9-3443		CHECKED J. Young 9-12-68	
9-2437-1 9-2811 9-3550		APPROVED M. R. Holcomb 9-12-68	
		APPROVED M. R. Holcomb 9-12-68	
The Bendix Corporation Electrical Components Division Sidney, New York			
TITLE: CONNECTOR, ELECTRICAL PLUG, TYPE PT-P10, MC, OLIVE DRAB			
SIZE	CODE IDENT NO.	71-453314	
C	77820		
SCALE	NONE	WT	SEE PARTS LIST
		REF	71-290630/44
		SHEET	