

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH — BASIC

CATALOG LISTING

BE-2RQ1-A4

BE-2RQ1-A4

DRAWING
NUMBER

ISSUE
4

REPLACES

RELEASE NO. PR-10343

CHECK

REVISIONS

A	CO-58782
	WJM
	25 JAN 86
B	CO-73287-G
	JAL
	20 OCT 93
C	CO-82133
	CSL
	26 JUL 96

CHECK

6 JULY 81

CEB

81


JUL

APR 16

FORMTEK

FO-52848-A

DRAWN




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ——— 14-22 OZ
RELEASE FORCE ——— 10 OZ MIN
DIFFERENTIAL TRAVEL — .0020-.0075
OVERTRAVEL ——— .094 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

25A-125 or 250VAC
1HP-125VAC; 2HP-250VAC
PILOT DUTY 750VA-125, 250, 277VAC
60/75°C (Cw)



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY 3 DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE:

NO PLACES	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
ONE PLACE	X	1/64	X	0.003
TWO PLACES	X,X	0.01/016	X,X	0.0005
THREE PLACES	X,X,X	0.001/008	X,X,X	0.0001
ANGLES				

SI METRIC

US CUSTOMARY

DESIGN UNITS

WEIGHT .084 LB