











Max. Temperature: 260°C during 10 seconds.
Find further technical information on DS 09550200301.

0955 156 6622 333	2	4-40 UNC	Black insulator	Samples
0955 156 3622 741	1			Reel packaging (140 connectors)
0955 156 6622 741	2			
0955 156 7622 741	3			
0955 156 3621 741	1	M3		
0955 156 6621 741	2			
0955 156 7621 741	3			
Part number	PL	Screw lock	Index designation	

		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.	
								Sub.	
		All rights reserved		Created by ZHUANGJ		Inspected by LUOK		Standardisation HOFFMANN	
Department EL PD						Date 2018-11-16		State Final Release	
HARTING Electronics GmbH D-32339 Espelkamp		Title D-Sub angled standard SMT 9-pole female ass with screw lock						Doc-Key / ECM-Nr. 100684631/UGD/001/C 500000141375	
		Type TB		Number 0955156X62X				Rev. C	Page 1/1