

All dimensions in mm	If in doubt - ask	©


Customer Information Sheet

Specifications:
Material:
Housing: Glass-filled PPS, UL94 V-0, black
Contact: Brass
Jackscrew: Stainless steel
Finish:
Contact: Gold
Packing:
Bag
For complete specification, see component specification C005XX (latest issue)




Scale 2:1





Section X-X



Partial section Y-Y

Order Code:
M80-562XX05
Total No. of Contacts:
04 to 50
(Even Numbers Only)

Table 1: Dimension Variants

Part No.	DIM 'A'	DIM 'B'	DIM 'C'
M80-5620405	2.00	9.00	14.0
M80-5620605	4.00	11.00	16.0
M80-5620805	6.00	13.00	18.0
M80-5621005	8.00	15.00	20.0
M80-5621205	10.00	17.00	22.0
M80-5621405	12.00	19.00	24.0
M80-5621605	14.00	21.00	26.0
M80-5621805	16.00	23.00	28.0
M80-5622005	18.00	25.00	30.0
M80-5622205	20.00	27.00	32.0
M80-5622405	22.00	29.00	34.0
M80-5622605	24.00	31.00	36.0
M80-5622805	26.00	33.00	38.0
M80-5623005	28.00	35.00	40.0
M80-5623205	30.00	37.00	42.0
M80-5623405	32.00	39.00	44.0
M80-5623605	34.00	41.00	46.0
M80-5623805	36.00	43.00	48.0
M80-5624005	38.00	45.00	50.0
M80-5624205	40.00	47.00	52.0
M80-5624405	42.00	49.00	54.0
M80-5624605	44.00	51.00	56.0
M80-5624805	46.00	53.00	58.0
M80-5625005	48.00	55.00	60.0

Notes:
1. Connectors are supplied with contacts loose.
2. For extra contacts, use part number M80-1940005.
3. For wire specification, gauge and type, see component specification C049XX (latest issue) for 22 AWG.
4. The recommended hand crimp tool is M22520/2-01 with positioner Z80-193. Refer to tooling instruction sheet IS-01 for complete crimping instructions.
5. The contact insertion and extraction tool is Z80-280. Refer to tooling instruction sheet IS-25 for assembly instructions.
6. Part M80-5622005 is used for illustration only. See Order Code.

Initials	Rev.	Date	CO
JW	5	07.07.26	36230
BMK	A	25.09.06	-----

HARWIN
www.harwin.com

This drawing and any information or descriptive matter set out hereon are confidential and copyright property of the Harwin group and must not be disclosed, loaned, copied or used for manufacturing, tendering or for any other purpose without their written permission.

TOLERANCES
X. = ±0.50mm
X.X = ±0.30mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
Angles = ±5°
Unless stated

Third angle projection

Sheet scale: 5:1
Do not scale
Sheet size: A3

MATERIAL: See above

FINISH: See above

Title: Datamate J-Tek DIL Male Plug Straight Cable Connector Kit, 22 AWG Reverse Fix

Drawing number: **M80-562XX05**

SHT 2 OF 2

Downloaded from Arrow.com.