



Part Number : [1200868853](#)

Product Description : Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 5 Poles, B-Coded, Male (Straight) to Pigtail, 0.25mm² Black PUR Cable, 1.0m (3.28') Length

Series Number : 120086

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 405006H08M010

Documents and Resources

Drawings

[1200868853_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 5 Poles, B-Coded, Male (Straight) to Pigtail, 0.25mm ² Black PUR Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Single Ended
UPC	191128974820

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	4.70mm (.185")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	B-Coded
LED Indicator	None

Material - Cable Jacket	PUR
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	125.000/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 21198
Wire Size (AWG)	24

This document was generated on Jun 10, 2026