


AI 0,75- 8 BU S1 - Ferrule



1200163

<https://www.phoenixcontact.com/us/products/1200163>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Dimensions according to DIN 46228-4, with color-coded plastic collars according to NF C 63-023:1994-02, for processing with the CRIMPFOX 4 in 1, Length contact range: 8 mm, sleeve length: 14 mm, color: blue, number of strips: 10, number of sleeves per strip: 50

Commercial data

Item number	1200163
Packing unit	500 pc
Minimum order quantity	500 pc
Sales key	BH34
Product key	BH3415
Catalog page	Page 415 (C-3-2019)
GTIN	4055626166551
Weight per piece (including packing)	0.091 g
Weight per piece (excluding packing)	0.091 g
Customs tariff number	85369010
Country of origin	DE

AI 0,75- 8 BU S1 - Ferrule



1200163
<https://www.phoenixcontact.com/us/products/1200163>

Technical data

Product properties


Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	For processing with CRIMPFOX 4 IN 1
	UL certified
	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of DIN 46228-1 and UL 486F in terms of size
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

Connection data

Conductor connection

Conductor cross section flexible max.	0.75 mm²
Conductor cross section AWG max.	18
Stripping length	11 mm

Dimensions

Dimensional drawing	
Sleeve length	14 mm
Length contact range	8 mm
Maximum stripping length	11 mm
Ferrule diameter	1.3 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.25 mm
Inner dimensions of the insulating collar	2.8 mm

Material specifications

Color	blue (RAL 5015)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

Mechanical properties

AI 0,75- 8 BU S1 - Ferrule

1200163

<https://www.phoenixcontact.com/us/products/1200163>



Technical data

Sleeve length	14 mm
---------------	-------

Environmental and real-life conditions

Ambient conditions

Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

Standards and regulations

Design according to standard	UL 486F-E, NF C 63-023
------------------------------	------------------------

AI 0,75- 8 BU S1 - Ferrule


1200163

<https://www.phoenixcontact.com/us/products/1200163>



Drawings

Dimensional drawing



AI 0,75- 8 BU S1 - Ferrule

1200163

<https://www.phoenixcontact.com/us/products/1200163>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1200163>



cULus Listed

Approval ID: E488001

AI 0,75- 8 BU S1 - Ferrule



1200163

<https://www.phoenixcontact.com/us/products/1200163>

Classifications

ECLASS

ECLASS-13.0	27400201
-------------	----------

ETIM

ETIM 9.0	EC000005
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

AI 0,75- 8 BU S1 - Ferrule



1200163
<https://www.phoenixcontact.com/us/products/1200163>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com