

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight cable plug (male)

11_BNC-50-4-54/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration		
Interface type	Gender	Standard
BNC	plug	IEC 61169-8_MIL-STD-348A/301_CECC 22120

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 2.5 GHz	27 dB	1.094
2.5 GHz ... 4 GHz	24 dB	1.135

Mechanical data	
Weight	0.01 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight cable plug (male)
11_BNC-50-4-54/133_N

Environmental data		
Operation temperature		-65 °C ... 165°C
Ordering Information Table		
Item number	Item description	Packaging type
84057622	11_BNC-50-4-54/133_NE	Single
Suitable cables		
Cable group		S16 - 4 mm / 50 Ohm
Suitable cables		SX_04272_D-02
Additional Information		
Remarks		El. Optimized for cable S_04172_D
Only as assembly		No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3682 / Date of publication: 25.11.2023 / uncontrolled copy