


PRODUCT NUMBER	PITCH
YK332xx0x0J0G	8.25 mm



DIMENSION	
Dim A	$N \times 8.25 + 2.0$
Dim B	$(N-1) \times 8.25$

N=Number of poles


Poles	Tolerance
2p-5p	$\pm 0.20$
6p-10p	$\pm 0.25$
11p-16p	$\pm 0.35$
17p-24p	$\pm 0.40$
25p-32p	$\pm 0.50$

PART NO.: YK 332xx 0 x 0 J00

No. of poles
02 2 poles
03 3 poles
...
32 32 poles

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant  
(lead<4%)  
In copper Alloy



RECOMMENDED P.C.B LAYOUT  
BOTTOM VIEW

MATERIALS & ELECTRICAL	cULus / CQC
RATED VOLTAGE & CURRENT:	300 V, 20 A / 300 V, 32 A
WITHSTAND VOLTAGE:	AC 2500V/Min
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG:	-40 °C +115 °C
SCREW TORQUE VALUE:	8.8 Lb-In
WIRE RANGE:	22 - 12 AWG
1) HOUSING:	Thermoplastic, UL 94 V-0 BLACK
2) TERMINAL:	BRASS, 0.8t
3) TERMINAL SCREWS:	STEEL, M3

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection	product family	TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified				
				angles $\phi$	X.±0.5	MM	TERMINAL BLOCK	
				XX	XX.±0.3			
				X.±1°	XX.X±0.1	scale	BARRIER TYPE	
		dr	EVAN LU	061614				
		engr	EVAN LU	061614		dwg no	sheet 1 of 1	size
		chr	HANKE FENG	061614				
		appd	SHI JUN	061614		FCJ	YK332xx0x0J0G	A4
sheet	revision	A						
index	sheet	1				type	CUSTOMER	Drawing