






DIMENSIONS



MODEL 4630 ACCELEROMETER

SPECIFICATIONS

- ◆ MEMS Triaxial Accelerometer
- ◆ DC Response, Ultra-Stable
- ◆ Accurate Temp Compensation
- ◆ Signal Conditioned Output
- ◆ 5,000g Over-Range Protection

The Model 4630 is an ultra-stable triaxial accelerometer offering both static and dynamic response. The silicon MEMS accelerometer incorporates integral temperature compensation that provides a stable output over a wide operating range. The three independent circuit assemblies have independent signal conditioning and can operate on common or separate power supplies. The advanced MEMS sensing elements are gas damped in order to provide a wide stable frequency response.

FEATURES

- ◆ Three Independent Circuits
- ◆ Low Current Consumption
- ◆ Ranges: $\pm 2g$ to $\pm 200g$
- ◆ Gas Damped, DC Response
- ◆ High Over-Range Protection
- ◆ -55°C to $+125^{\circ}\text{C}$ Operating Range
- ◆ Low Transverse Sensitivity

APPLICATIONS

- ◆ Transportation
- ◆ Vibration/Shock Monitoring
- ◆ Road Vehicle Testing
- ◆ Low Frequency Applications
- ◆ Modal Analyses

X-AXIS	Y-AXIS	Z-AXIS
BLK/BLU	BLK/YEL	BLK
WHT/BLU	WHT/YEL	WHT
RED/BLU	RED/YEL	RED
GRN/BLU	GRN/YEL	GRN
BRN/BLU	BRN/YEL	BRN

PERFORMANCE SPECIFICATIONS

All values are typical at +24°C, 80Hz and 12Vdc excitation unless otherwise stated. Measurement Specialties reserves the right to update and change these specifications without notice.

Parameters

DYNAMIC

	±2	±5	±10	±20	±30	±50	±100	±200	Notes
Range (g)	1000	400	200	100	67	40	20	10	
Sensitivity (mV/g)	0-200	0-600	0-800	0-800	0-800	0-800	0-1000	0-1000	±5% ¹
Frequency Response (Hz)	700	800	1000	1500	1500	4000	6000	8000	
Natural Frequency (Hz)	±0.5	±0.5	±0.5	±0.5	±0.5	±0.5	±0.5	±0.5	
Non-Linearity (%FSO)	<3	<3	<3	<3	<3	<3	<3	<3	<1 Typical
Transverse Sensitivity (%)	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.6	
Damping Ratio	2000	5000	5000	5000	5000	5000	5000	5000	
Shock Limit (g)	550	700	750	1100	750	750	800	800	Passband
Residual Noise (µV RMS)	38	71	126	379	378	632	1265	2530	Passband
Spectral Noise (µg/√Hz)									

ELECTRICAL

Zero Acceleration Output (mV)	±50								Differential
Excitation Voltage (Vdc)	8 to 36								
Excitation Current (mA)	<15 (<5 per channel)								
Bias Voltage (Vdc)	2.5								
Output Resistance (Ω)	<100								
Full Scale Output Voltage (V)	±2								
Insulation Resistance (MΩ)	>100								@100Vdc
Turn On Time (msec)	<100								
Ground Isolation	Isolated from Mounting Surface								

ENVIRONMENTAL



Thermal Zero Shift (%FSO/°C)	±0.004								Typical
Thermal Sensitivity Shift (%/°C)	±0.010								Typical
Operating Temperature (°C)	-55 to 125								
Storage Temperature (°C)	-55 to 125								
Housing (Active Element & Electronics)	Hermetic Solder Seal								
Humidity (Housing)	Epoxy Seal, IP65								

PHYSICAL

Case Material	Anodized Aluminum
Cable	15x #30 AWG Conductors PFA Insulated Leads, Braided Shield, TPE Jacket
Weight (grams)	40
Mounting	2x #4 or M3 Screws
Mounting Torque	6 lb-in (0.7 N-m)

Calibration supplied:	CS-FREQ-0100	NIST Traceable Amplitude Calibration from 20Hz to ±5% Frequency Response Limit ¹
Supplied accessories:	AC-D02855	2x #4-40 (1 ^{1/8} length) Socket Head Cap Screw and Washer
Optional accessories:	121	3-Channel Precision Low Noise DC Amplifier

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the right to make changes without further notice to any product herein. Measurement Specialties, Inc. makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does Measurement Specialties, Inc. assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. Measurement Specialties, Inc. does not convey any license under its patent rights nor the rights of others.



ORDERING INFORMATION

4630	GGG	ZZZ	C
Series Type			
Range			
002=2g			
005=5g			
010=10g			
020=20g			
030=30g			
050=50g			
100=100g			
200=200g			
Cable length			
060=60 inches			
120=120 inches			
180=180 inches			
240=240 inches			
300=300 inches			
360=360 inches			
480=480 inches			
600=600 inches			
197=197 inches, 5 meters			
394=394 inches, 10 meters			

Example; 4630-010-060-C
Model 4630, 10g range, 60inch cable length

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Tel: 800-522-6752
Email: customercare.hmpt@te.com

EUROPE

MEAS France SAS
a TE Connectivity Company
Tel: 800-440-5100
Email: customercare.lcsb@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Tel: 0400-820-6015
Email: customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.