Part Number : 1300480358
Product Description : Micro-Change (M12) to Standard RJ-45 Double-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Male RJ-45 (Straight), 24 AWG, Teal Unshielded TPE Cat5e Cable, 25.0m (82.02') Length
Series Number : 130048
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : E16A06004M250



Documents and Resources

Drawings

1300480358_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130048
Description	Micro-Change (M12) to Standard RJ-45 Double-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Male RJ-45 (Straight), 24 AWG, Teal Unshielded TPE Cat5e Cable, 25.0m (82.02') Length
IP Rating	IP67
Performance Category	5e
Product Name	Micro-Change (M12),Industrial Ethernet,RJ45
Protocol	EtherNet
Type	Double Ended
UPC	78172551787

Agency

UL	E200650

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	6.10mm (.240")
Cable Length	25.0m (82.02')

Downloaded from Arrow.com.

Color - Cable Jacket	Teal
Connector End A	Micro-Change (M12)
Connector End B	RJ-45 (standard)
Coupling Style	Threaded
Gender	Male-Male
Keyway	D-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	PUR
Material - Contact	Copper Alloy, Phosphor Bronze
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	25663.000/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +75°C
Wire/Cable Type	Unshielded TPE/AWM 2463
Wire Size (AWG)	24

Downloaded from Arrow.com.