

CMPT591E**ENHANCED SPECIFICATION
SURFACE MOUNT
PNP SILICON TRANSISTOR**
www.centrasemi.com
DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMPT591E type is an Enhanced version of the industry standard 591 PNP silicon transistor. This device is manufactured by the epitaxial planar process and epoxy molded in an SOT-23 surface mount package. The CMPT591E features Low $V_{CE(SAT)}$, high h_{FE} , and has been designed for high current general purpose amplifier applications.

MARKING CODE: C59**COMPLEMENTARY TYPE: CMPT491E****SOT-23 CASE****FEATURED ENHANCED SPECIFICATIONS:**

* $V_{CE(SAT)}$ @ 1.0A = 0.6V MAX (from 0.4V MAX)

* h_{FE} @ 500mA = 200 MIN (from 100 MIN)

MAXIMUM RATINGS: ($T_A=25^\circ\text{C}$)

	SYMBOL		UNITS
Collector-Base Voltage	V_{CBO}	80	V
Collector-Emitter Voltage	V_{CEO}	60	V
Emitter-Base Voltage	V_{EBO}	5.0	V
Continuous Collector Current	I_C	1.0	A
Continuous Base Current	I_B	200	mA
Peak Collector Current	I_{CM}	2.0	A
Power Dissipation	P_D	350	mW
Operating and Storage Junction Temperature	T_J, T_{stg}	-65 to +150	$^\circ\text{C}$
Thermal Resistance	θ_{JA}	357	$^\circ\text{C/W}$

ELECTRICAL CHARACTERISTICS: ($T_A=25^\circ\text{C}$ unless otherwise noted)

SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNITS
I_{CBO}	$V_{CB}=60\text{V}$			100	nA
I_{EBO}	$V_{EB}=4.0\text{V}$			100	nA
BV_{CBO}	$I_C=100\mu\text{A}$	80			V
BV_{CEO}	$I_C=10\text{mA}$	60			V
BV_{EBO}	$I_E=100\mu\text{A}$	5.0			V
* $V_{CE(SAT)}$	$I_C=500\text{mA}, I_B=50\text{mA}$			0.20	V
* $V_{CE(SAT)}$	$I_C=1.0\text{A}, I_B=100\text{mA}$			0.40	V
* $V_{BE(SAT)}$	$I_C=1.0\text{A}, I_B=100\text{mA}$			1.1	V
$V_{BE(ON)}$	$V_{CE}=5.0\text{V}, I_C=1.0\text{A}$			1.0	V
* h_{FE}	$V_{CE}=5.0\text{V}, I_C=1.0\text{mA}$	200			
* h_{FE}	$V_{CE}=5.0\text{V}, I_C=500\text{mA}$	200		600	
h_{FE}	$V_{CE}=5.0\text{V}, I_C=1.0\text{A}$	50			
h_{FE}	$V_{CE}=5.0\text{V}, I_C=2.0\text{A}$	15			
f_T	$V_{CE}=10\text{V}, I_C=50\text{mA}, f=100\text{MHz}$	150			MHz
C_{ob}	$V_{CB}=10\text{V}, I_E=0, f=1.0\text{MHz}$		14	20	pF

* Enhanced specification


R4 (28-February 2024)

CMPT591E

**ENHANCED SPECIFICATION
SURFACE MOUNT
PNP SILICON TRANSISTOR**



SOT-23 CASE - MECHANICAL OUTLINE



LEAD CODE:

- 1) Base
- 2) Emitter
- 3) Collector

MARKING CODE: C59

DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.003	0.007	0.08	0.18
B	0.006	-	0.15	-
C	-	0.005	-	0.13
D	0.035	0.044	0.89	1.12
E	0.110	0.120	2.80	3.05
F	0.075		1.90	
G	0.037		0.95	
H	0.047	0.055	1.19	1.40
I	0.083	0.104	2.10	2.64
J	0.014	0.020	0.35	0.50

SOT-23 (REV: R4)

R4 (28-February 2024)

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centrasemi.com

Worldwide Field Representatives:
www.centrasemi.com/wwreps

Worldwide Distributors:
www.centrasemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centrasemi.com/terms