



WITH ATTACHMENT



ATTACHMENT OPTIONS:



OMIT FOR NO ATTACHMENT
(SEE SHEET 2)

PCMMP-10-1-C-WR4-03

PROTECTION COVER —
TO FIT MIGHTY MOUSE (801 SERIES) —
PLUG FITTING —
INSERT F FOR —
FLUOROSILICONE GASKET —
OMIT FOR STANDARD —
SILICONE GASKET —
SHELL SIZE (TABLE 1) —
MATERIAL (TABLE 5) —
FINISH (TABLE 6) —
LANYARD TYPE (TABLE 4) —
LANYARD LENGTH (IN INCHES) —
ATTACHMENT (SEE ABOVE) —


DRAWN		DIW		DATE 25/02/2014			3RD ANGLE PROJECTION NOT TO SCALE		PART NUMBER: PCMMP SERIES					 Polamco 						
SALES APPR				25/02/2014			TITLE: PLUG PROTECTION COVER													
DESIGN APPR						UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 1°		ASSY USED ON: MIGHTY MOUSE 801 SERIES												
PROD APPR																				
QUAL APPR																				
ISSUE		REV.		DCR		MATERIAL SEE TABLE 5		FINISH SEE TABLE 6		THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.					POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP		SHT 1		DRAWING NO: P14628	
AA				7332																
NCAGE CODE U5792				WEIGHT		---														

TABLE 1

SHELL SIZE	A THREAD	ØB MAX	ØC MIN
05	0.3125-0.05P-0.1L	11,8	5,85
06	0.3750-0.05P-0.1L	13,3	6,85
07	0.4375-0.05P-0.1L	15,0	8,60
08	0.5000-0.05P-0.1L	16,6	9,90
09	0.5625-0.05P-0.1L	18,1	11,45
10	0.6250-0.05P-0.1L	19,7	13,35
13	0.8125-0.1P-0.2L	24,5	16,55
16	1.0000-0.1P-0.2L	29,2	-
17	1.0625-0.1P-0.2L	30,8	22,85
21	1.3125-0.1P-0.2L	37,5	-

*PLEASE CONSULT FACTORY FOR DIMENSIONS NOT LISTED ABOVE

TABLE 2

EYELET REF.	ØF
01	3,2
02	3,7
03	4,3
04	5,3
05	6,4

TABLE 3

RING REF.	ØE
05	8,1
06	10,0
07	11,9
08	13,0
09	15,1
10	16,1
13	18,0
16	24,6
17	24,6
21	30,6

TABLE 4

CODE	LANYARD TYPE
WR	NYLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
TC	TEFLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
WG	TEFLON COVERED (OLIVE DRAB) STAINLESS STEEL WIRE ROPE
WB	TEFLON COVERED (BLACK) STAINLESS STEEL WIRE ROPE
WRB	PVC COVERED (BLACK) STAINLESS STEEL WIRE ROPE
LC	LINK CHAIN
BK	BLACK CORD
VGB	1,5mm BLACK POLYESTER CORD EQV. TO DIN83330-E1,5
R	OLIVE DRAB POLYESTER CORD
NB	OLIVE DRAB NYLON CORD
NK	BLACK NYLON CORD

TABLE 5

CODE	MATERIAL
1	ALUMINIUM
2	NICKEL ALUMINIUM BRONZE
4	STAINLESS STEEL
7	BLACK ACETAL
74	COMPOSITE


LIST NOT EXHAUSTIVE, SEE MATERIAL TABLE FOR OTHER OPTIONS

TABLE 6


CODE	DESCRIPTION
B	CADMIUM, OLIVE DRAB OVER ELECTROLESS NICKEL
C	ELECTROLESS NICKEL
G	BLACK ANODISE, SULPHURIC
J	PASSIVATE
U	UNPLATED CLEAN FINISH NOT SHOT BLASTED
Z	SHOT BLAST FOR NON-REFLECTIVE FINISH
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
ZN	ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL

LIST NOT EXHAUSTIVE, SEE PLATING TABLE FOR OTHER OPTIONS


WITHOUT ATTACHMENT




PCMMP-**-**-LG



PCMMP-10-1-C
NO ATTACHMENT VERSION



PCMMP-10-1-C-EO
EYELET ONLY VERSION
(NO LANYARD)

DRAWN	DIW		DATE 25/02/2014	 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER: PCMMP SERIES				 Polamco 			
SALES APPR			25/02/2014		TITLE: PLUG PROTECTION COVER							
DESIGN APPR				UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 1°	ASSY USED ON: MIGHTY MOUSE 801 SERIES							
PROD APPR												
QUAL APPR				MATERIAL SEE TABLE 5	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.					POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP	SHT 2	DRAWING NO: P14628
ISSUE AA	REV.	DCR 7332										
NCAGE CODE U5792			WEIGHT ---									