Specifications



Eaton PHV-5R4V155-R

Eaton PHV supercapacitor, 5.4 V, 1.5 F, 0.16 Ω, Vertical Pack

General specifications	
PRODUCT NAME	Eaton PHV cylindrical cell supercapacitor pack
CATALOG NUMBER	PHV-5R4V155-R
UPC	051712353809
PRODUCT LENGTH/DEPTH	17.3 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	9 mm
PRODUCT WEIGHT	3 g
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Recognized
PRODUCT TYPE	Cylindrical cell supercapacitor pack

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

PACKING	Bulk
CONTACT CONFIGURATION	Vertical
SIZE	16.8 x 8.5 x 21.5 mm
TERMINALS	Through hole
SHAPE	Rectangular
DC EQUIVALENT SERIES RESISTANCE (ESR)	0.16 Ω
OPERATING TEMPERATURE RANGE	-40 °C to +65 °C
SERIES	PHV
MAX VOLTAGE	5.4 V
CAPACITANCE	1.5 F
LEAKAGE	18 µ A
ENERGY	21.9 J
POWER	46 W
PEAK CURRENT (1 SEC)	3.3 A
CAPACITANCE END OF LIFE RATING	70%
ESR END OF LIFE RATING	200%
GRADE	Industrial

Resources

APPLICATION NOTES	High power supercapacitors enable new power applications and replace batteries Supercapacitor soldering guidelines
BROCHURES	Supercapacitor selection guide Eaton's electronics components portfolio overview brochure
SPECIFICATIONS AND DATASHEETS	Eaton PHV supercapacitor data sheet Eaton Specification Sheet - PHV-5R4V155-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.