

M23 12 Male -solder (termination)CCW




Image is for illustration purposes only. Please refer to product description.

Part number	09 15 112 2612
Specification	M23 12 Male -solder (termination)CCW
HARTING eCatalogue	https://harting.com/09151122612

Identification

Category	Inserts
Series	Circular connectors M23
Identification	Signal
Element	Inserts
Specification	Marking in opposite direction

Version

Termination method	Solder termination
Gender	Male
Number of contacts	12

Technical characteristics

Conductor cross-section (mm ²)	1 mm ² max.
Rated current	8 A
Rated voltage	200 V
Rated impulse voltage	2.5 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polyamide (PA)
-------------------	----------------



Pushing Performance
Since 1945

Material properties

Colour (insert)	White
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	052d6da0-30ef-44e8-bbe4-e75780521d22
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	6.4 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140187191
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421