

## Features/Benefits

- 2 axis, multi-direction operation
- 2,000,000 life cycle for toggle
- Center select momentary switch
- Small package size

## Typical Applications

- Gaming peripherals
- Remote Control Vehicles
- Mini-joystick
- Thumb control
- Navigation control
- Industrial control
- Heavy equipment



## Electrical

TOTAL RESISTANCE (POTENTIOMETERS):  $10k\Omega \pm 20\%$  initial  
Within  $\pm 20\%$  of initial values for 10,000 cycles

RESISTANCE POTENTIOMETERS: Percentage of the voltage of terminal 1-2 to the voltage of terminal 1-3

RATED VOLTAGE: 50 VAC or 5 VDC

RATED POWER: 0.05 A @ 12 VDC

CONTACT NOISE: Noise < 10% of operating voltage

VOLTAGE DIVIDER: 39.6 ~ 60.4%

INSULATION RESISTANCE: > 100 M $\Omega$

WITHSTANDING VOLTAGE: No arcing or breakdown

## Mechanical

PATTERN OF ACTUATOR MOVEMENT: Toggle cross-wide and in a circle

FULL STROKE ACTUATION STOP STRENGTH: > 3.1 kgf  
(3 seconds minimum)

PULL STRENGTH OF THE ACTUATOR: > 5.0 kgf  
(3 seconds minimum)

ACTUATION FORCE: 120 +/- 50 gf (12 +/- 5mN\*M of Torque)

ACCURACY OF RETURN TO ACTUATOR RELEASE POSITION:  $\pm 3^\circ$

TOGGLE ANGLE OF OPERATION:  $26^\circ$  max. angle from vertical  
through full circular range of rotation

OPERATING LIFE: 1,000,000 cycles minimum (center switch)  
2,000,000 cycles minimum (thumbstick toggle)

## Environment

OPERATING TEMPERATURE:  $-10^\circ\text{C}$  to  $+70^\circ\text{C}$


STORAGE TEMPERATURE:  $-30^\circ\text{C}$  to  $+80^\circ\text{C}$

## Packaging


Tray (60 units)

## How To Order

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.



\* Please note some option codes are mutually exclusive. Consult factory if you have any questions



First Angle  
Projection

Dimensions are shown: mm  
Specifications and dimensions subject to change



