








Size	
Length(L)	1.60mm +/-0.15mm
Width(W)	0.80mm +/-0.15mm
Thickness(T)	0.80mm +/-0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.

Electrical Characteristics	
Inductance	1.2uH +/-20% at 10MHz
Rated Current	50mA
Self-Resonant Frequency [Min.]	110MHz
Self-Resonant Frequency [Typ.]	150MHz
Q [Min.]	35 at 10MHz
Q [Typ.]	50 at 10MHz
DC Resistance [Nom.]	250mΩ
DC Resistance [Max.]	650mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.
Weight	0.004g

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



Products

» Search by Part No. » Search by Characteristics » Distributor Inventory Check

» Capacitors

» Inductors (Coils)

» EMC Components

» RF / SAW Components and Modules

» Voltage Protection Devices

» Current Protection Devices

» Temperature Protection Devices

» Sensors and Sensor Systems

» Ceramic Switching / Heating, Piezo Components and Buzzers

» Transformers

» Ferrites and Accessories

» Noise Suppression Sheets / Magnetic Sheets

» Anechoic Chambers and Radio Wave Absorbers

» Power Supplies

» Magnets

» Flash Storage

» Wireless Charging

» FA Systems

» ITO Transparent Conductive Film

» Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB)

Application Guides

Technical Support

Tech Library

Environment

Contact

News

Home

About TDK

TDK Worldwide