Part Number : 791098609
Product Description : Milli-Grid Vertical Receptacle, 2.00mm Pitch, Dual Row, Surface Mount, Top/Bottom Entry, with Press-fit Plastic Pegs, with Cap, Tape and Reel, 0.38µm Gold (Au) Plating, 20 Circuits, Lead-Free
Series Number : 79109
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

791098609_sd.pdf

PK-70873-0259-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

503940001-AS-000.pdf

PS-79107-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	79109
Description	Milli-Grid Vertical Receptacle, 2.00mm Pitch, Dual Row, Surface Mount, Top/Bottom Entry, with Press-fit Plastic Pegs, with Cap, Tape and Reel, 0.38µm Gold (Au) Plating, 20 Circuits, Lead-Free
Application	Board-to-Board, Signal
Component Type	PCB Receptacle
Product Name	Milli-Grid
UPC	822348492817

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Downloaded from Arrow.com.

Physical

Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	0.546/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.381µm
Plating min - Termination	1.880µm
Polarized to Mating Part	No
Polarized to PCB	No
Robotic Placement	Pick and Place Cap
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Surface Mount

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
Milli-Grid Vertical Through Hole Headers	87758
Milli-Grid Vertical Surface Mount Headers	87759
Milli-Grid Right-Angle Through Hole Headers	87760
Milli-Grid Vertical, Dual Row, Through Hole Headers	87831
Milli-Grid Vertical, Dual Row, Surface Mount Headers	87832
Milli-Grid Right-Angle Dual Row Through Hole Headers	87833
Milli-Grid Vertical, Dual Row, Through Hole Headers	151117
Milli-Grid Vertical, Dual Row, Surface Mount Headers	151118
Milli-Grid Right-Angle, Dual Row, Through Hole Headers	151119
Milli-Grid Right-Angle, Dual Row, Surface Mount Headers	151120

Downloaded from Arrow.com.