HellermannTyton

Technical data sheet

Article number:
315-50320 TR27-3.2/1.6



Product Group	Heat shrinkable tubing 2:1 - Flame retardant
Product Family	TR27
Material	Polyolefin, cross-linked (PO-X)
Colour	Black (BK)

Behaviour at Heat Shock	not cracking, not dripping, not fluid
Dielectric Strength [Test method]	15 kV/mm [IEC 684 P2]
Elongation at break (min.)	200 %
Heat Shock Test	4h/150°C
Longitudinal Change After Shrinkage	+5%/-10% max.
Min. Shrink Temperature - °C	+115 °C
Operating Temperature	-40 °C to +105 °C
Package Content	150 m
Package Content packed in	meter
Recov. Ø d max.	1.6 mm
Shrink Ratio	2:1
Specifications	EN 45545-2
Supplied Ø D min.	3.2 mm
Tensile Strength	7 MPa
Wall (WT)	0.51 mm
Water Absorption	1.0 %

HF ✓ LFH ✓ RoHS ✓

EN 45545-2

created on 5. June 2026, 4:08 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.