

Representative Image

Catalog No. TY528M

Description: CBL TIE 50LB 14 NAT NYLON 2-PC D

UPC No 786210805139

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum or as a Flexible Cable and Conduit Support, Length of 360.5mm (14.2 Inches), Width of 4.82mm (0.19 Inches), Thickness of 1.4mm (0.05 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds , 222 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Dimensions

Width	0.19 in , 4.9 mm
Length	14.2 in , 361 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	0.12 to 4.02 in , 3 to 102 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

by ABB

Downloaded from Arrow.com.

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.