



**Part Number :** [190130026](#)  
**Product Description :** InsulKrimp Fully Insulated Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 22-18 AWG, Expanded Red Insulator, Mylar Tape  
**Series Number :** 19013  
**Status :** Active  
**Product Category :** Quick Disconnects  
**Engineering Number :** AA-2317T



Documents & Resources


**Drawings**  
[190130026\\_sd.pdf](#)

**3D Models and Design Files**  
[190130026\\_stp.zip](#)

**Specifications**  
[PS-19902-008-001.pdf](#)  
[PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
  - REACH SVHC
  - Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Quick Disconnects
Series	19013
Description	InsulKrimp Fully Insulated Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 22-18 AWG, Expanded Red Insulator, Mylar Tape
Product Name	InsulKrimp
Type	Quick Disconnect
UPC	822350961455

#### Agency

CSA	LR18689
UL	E79133

#### Electrical

Voltage - Maximum	600V AC
-------------------	---------

#### Physical

Barrel Type	Closed - Brazed
Color - Resin	Red
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)

Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.231/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	105°C
Wire Insulation Diameter	3.50mm max.
Wire Size (AWG)	18, 20, 22

---

## Application Tooling

### Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>198132010</u>
Mini-Mac Applicator	<u>638852300</u>
Hand Crimp Tool	<u>640016300</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640056300</u>

---

This document was generated on Feb 13, 2025