


© 2026 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G12	PART STATUS CHANGE TO DISCONTINUNACE	14JUL2026	NS	PS





796635-3 AS SHOWN



1. MATERIALS AND FINISH:
   HOUSING: PA 6-6, UL 94-V0, COLOR:BLACK.
   CLAMP: BRASS, NICKEL PLATED.
   CONTACT SPRING: PHOSPHOR BRONZE, FINISH: SEE TABLE.
   CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2. END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.

3. WIRE SIZE RANGE: 12-30 AWG.

4. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
   UNDERWRITERS LABORATORIES INC.FILE N° E60677.

5. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.

△6 INK MARKING, WHITE COLOR.

MARKING	CONTACT FINISH	L	NO OF POSN	PART NUMBER
OBSOLETE	-	0.8µm GOLD	106.68±0.35	21	5-796635-8
OBSOLETE	-	0.8µm GOLD	86.36±0.30	17	5-796635-7
OBSOLETE	-	0.8µm GOLD	71.12	14	5-796635-6
OBSOLETE	-	0.8µm GOLD	60.96	12	5-796635-5
OBSOLETE	-	0.8µm GOLD	50.80	10	5-796635-4
OBSOLETE	-	0.8µm GOLD	40.64	8	5-796635-3
OBSOLETE	-	0.8µm GOLD	35.56	7	5-796635-2
OBSOLETE	-	0.8µm GOLD	30.48	6	5-796635-1
OBSOLETE	-	0.8µm GOLD	25.40	5	5-796635-0
OBSOLETE	-	0.8µm GOLD	20.32±0.15	4	4-796635-9
OBSOLETE	-	0.8µm GOLD	15.24±0.15	3	4-796635-8
OBSOLETE	-	0.8µm GOLD	10.16±0.15	2	4-796635-7
	DETAIL R	TIN	45.72	9	4-796635-6
OBSOLETE	DETAIL P	TIN	10.16±0.15	2	4-796635-5
OBSOLETE	-	0.8µm GOLD	20.32±0.15	4	4-796635-4
OBSOLETE	-	0.8µm GOLD	45.72	9	4-796635-3
	DETAIL N	TIN	86.36±0.30	17	4-796635-2
	DETAIL M	TIN	66.04	13	4-796635-1
	DETAIL L	TIN	60.96	12	4-796635-0
	DETAIL K	TIN	15.24±0.15	3	3-796635-9
	DETAIL J	TIN	81.28±0.30	16	3-796635-8
	DETAIL H	TIN	15.24±0.15	3	3-796635-7
OBSOLETE	-	GOLD	30.48±0.20	6	3-796635-6
	-	TIN	127.00±0.35	25	2-796635-5
	-	TIN	121.92±0.35	24	2-796635-4
OBSOLETE	-	TIN	116.84±0.35	23	2-796635-3
	-	TIN	111.76±0.35	22	2-796635-2
	-	TIN	106.68±0.35	21	2-796635-1
OBSOLETE	-	TIN	101.60±0.35	20	2-796635-0
OBSOLETE	-	TIN	96.52±0.35	19	1-796635-9
	-	TIN	91.44±0.30	18	1-796635-8
	-	TIN	86.36±0.30	17	1-796635-7
	-	TIN	81.28±0.30	16	1-796635-6
	-	TIN	76.20±0.30	15	1-796635-5
	-	TIN	71.12	14	1-796635-4
	-	TIN	66.04	13	1-796635-3
	-	TIN	60.96	12	1-796635-2
OBSOLETE	-	TIN	55.88	11	1-796635-1
	-	TIN	50.80	10	1-796635-0
	-	TIN	45.72	9	796635-9
	-	TIN	40.64	8	796635-8
	-	TIN	35.56±0.20	7	796635-7
	-	TIN	30.48±0.20	6	796635-6
	-	TIN	25.40±0.20	5	796635-5
	-	TIN	20.32±0.15	4	796635-4
	-	TIN	15.24±0.15	3	796635-3
	-	TIN	10.16±0.15	2	796635-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.3
2 PLC ±0.25
3 PLC ±0.000
4 PLC ±0.0000
ANGLES ±2°

MATERIAL -
FINISH -

DWN S.WELDON 18OCT2000
CHK D. BIEVENOUR 18OCT2000
APVD D. BIEVENOUR 18OCT2000
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME TERMINAL BLOCK, PLUG, STACKING, 5.08mm PITCH
-


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-796635	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 2 | REV G12


Downloaded from Arrow.com.

© 2026 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




6 DETAIL H




6 DETAIL J




6 DETAIL K




6 DETAIL L




6 DETAIL M



6 DETAIL N



6 DETAIL R



6 DETAIL P

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.WELDON 18OCT2000	TE Connectivity
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.2 2 PLC ±0.0 3 PLC ±0.000 4 PLC ±0.0000 ANGLES ±2°	CHK D. BIEVENOUR 18OCT2000	NAME TERMINAL BLOCK, PLUG, STACKING, 5.08mm PITCH -
		APVD D. BIEVENOUR 18OCT2000	
		PRODUCT SPEC -	
		APPLICATION SPEC -	SIZE A2 / CAGE CODE 00779 / DRAWING NO C-796635 / RESTRICTED TO -
MATERIAL -	FINISH -	WEIGHT -	CUSTOMER DRAWING / SCALE 2:1 / SHEET 2 OF 2 / REV G12

Downloaded from Arrow.com.