
SPECIFICATION CONTROL DRAWING

55/P1124

TITLE	Date	Revision
TWO CONDUCTOR CABLE, SHIELDED, JACKETED, OUTER SPACE, 600 VOLT	6-22-05	A

This specification sheet forms a part of the latest issue of Raychem Specification 55/.



CABLE CONSTRUCTION DETAILS

PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55/P1124-30-*	30	38	.006	.008	.081	.086	5.4
55/P1124-28-*	28	38	.006	.008	.087	.092	6.3
55/P1124-26-*	26	38	.006	.008	.097	.102	7.9
55/P1124-24-*	24	38	.006	.008	.107	.112	9.8
55/P1124-22-*	22	38	.006	.008	.119	.125	12.4
55/P1124-20-*	20	38	.006	.008	.133	.140	16.4
55/P1124-18-*	18	38	.006	.008	.153	.161	21.9
55/P1124-16-*	16	38	.006	.008	.169	.177	26.6

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C
Maximum continuous conductor temperature
VOLTAGE RATING: 600 volts (rms) at sea level
CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour
DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz
JACKET COLOR: White preferred
JACKET ELONGATION: 50% (minimum)
JACKET FLAWS:
Spark Test, 1000 volts (rms)
Impulse Dielectric Test, 6.0 kV (peak)
RADIATION RESISTANCE: 500 megarads

SHIELD COVERAGE: 85% (minimum)
VACUUM STABILITY:
Total Mass Loss (TML), 1.0% (maximum)
Volatile Condensable Material, 0.1% (maximum)
VOLTAGE WITHSTAND TEST (Post Environmental):
1500 volts (rms), 60 Hz, 1 minute

PART NUMBER:
The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.
1/ Example: AWG 22, black and brown component wires; white jacket: 55/P1124-22-0/1-9

NOTE: Nominal values are for information only.
Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

tyco Electronics
Raychem Wire & Cable
501 Oakside Avenue
Redwood City, CA 94063-3800
Phone: 1-800-227-8816
Fax: 1-650-361-6297

© 2005 Tyco Electronics Corporation. All rights reserved.

Downloaded from Arrow.com.