


 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Receptacle
- ? HV-100
- ? Number of Positions = 20
- ? Number of Rows = Dual
- ? Standard Profile

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

[HV 100 VERTICAL CONNECTOR](#) (PDF, English)

? None Available

? None Available

? None Available

? None Available

? None Available

? Product Line Information

? PCB Layout

? Tooling

List all Documents

Product Type Features:

- ? Product Type = Receptacle
- ? Connector Series = HV -100
- ? Number of Positions = 20
- ? Profile = Standard
- ? Mount Angle = Vertical
- ? Mounting Pattern (mm [in]) = 2.54 x 2.54 [.100 x .100]
- ? Sealed = Yes
- ? Holddown Feature = Without
- ? PCB Retention Feature = Yes
- ? Closed Entry = With
- ? Board Standoff = With

? Stackable = Yes

? Termination Method = Through Hole

? Termination (Solder) Post Length (mm [in]) = 3.10 [0.122]

? Number of Rows = Dual

? Connector Height (mm [in]) = 8.50 [0.335]

? Centerline, Matrix (mm [in]) = 2.54 [.100]

? PCB Retention Method = Retention Solder Tails

? Closed Bottom = Without

? Contact Mating Area Plating Material = Tin
 ? Contact Material = Phosphor Bronze

? Housing Entry Style = Top
 ? Housing Material = Polyester GV
 ? Housing Flammability Rating = UL 94V -0
 ? Housing Color = Green

- ? Government/Industry Qualification = No
- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Brand = AMP