



## RT 100, 140, 250 Series Releasable Ties

### Features and Benefits

These easily released cable ties are manufactured in PA12 giving them excellent weather resistance, making them ideal for outdoor applications. The outside serrated design ensures that whilst gripping the bundle surface tightly they do not cause indentation or damage to the insulation or hose, especially in vibration environments.

### Application


These releasable and reusable cable ties are ideal for temporary or permanent installation in a wide variety of applications in industries as diverse as: automotive, construction and panel building.



RT250 tie used as a hose fixing in a car engine compartment.

### Material Data

Material	<b>Polyamide 12 (PA12)</b>
Operating Temperature	<b>-40 °C to +85 °C Continuous, (+105 °C for 500 h)</b>
Flammability	<b>UL94 HB</b>



RT Series

### Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Colour
131-11120	<b>RT100</b>	100	7.0	23.0	170	PA12	Black (BK)
131-11420	<b>RT140</b>	140	9.0	36.0	190	PA12	Black (BK)
131-12520	<b>RT250</b>	250	9.0	71.0	190	PA12	Black (BK)

All dimensions in mm. Subject to technical changes.