


REV.	DATE	DESCRIPTION
A	08/20/98	ADD TEFLON INSULATOR
B	05/01/04	UPDATE DRAWING FORMAT
C	10/10/07	REMOVE CHAMFER FROM CENTER CONTACT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex				
7						DRAWN	G.R.S.	10/10/07						
6						CHECKED			PART DESCRIPTION SMA PANEL RECEPTACLE JACK					
5						ISSUED								
4						SHEET	1 OF 1			PART NO. 132150				
3	CONTACT PIN	BER. COPPER	GOLD	1	CAD FILE			DWG. NO. 132150.DWG						
2	INSULATOR	TEFLON	NATURAL	1	C:/132/132150.DWG								REV. C	
1	BODY	BRASS	GOLD	1	DO NOT SCALE DRAWING									
DESCRIPTION		MATERIAL	FINISH	QTY										