

**MICRO SWITCH**  
a Honeywell Division

FED. MFG. CODE 91929

# SWITCH — BASIC

CATALOG LISTING

V3L-708

CQ-H0711

CATALOG LISTING  
V3L-708  
PAGE 1 OF 1

ISSUE  
6

REVISIONS  
A OBS  
0079950  
CSL  
15 MAR 95  
B REINST  
PR21678  
DCS  
1 JUN 95

REPLACES

RELEASE NO. PR-12429

CHECK


CHECK

CHECK

1 JUN 95

DCS


DDM/CAD



ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



| CHARACTERISTICS                  | ELECTRICAL DATA                                                                           | SCALE FULL                                   | DO NOT<br>SCALE PRINT |
|----------------------------------|-------------------------------------------------------------------------------------------|----------------------------------------------|-----------------------|
| OPERATING FORCE — — — 4 OZ MAX   | CONTACT ARRANGEMENT<br>S P D T                                                            | UNLESS OTHERWISE SPECIFIED<br>TOLERANCES ARE |                       |
| RELEASE FORCE — — — 1/2 OZ MIN   | L156 11A 1/3HP 125, <u>250</u> OR 277 VAC<br>1/2A 125 VDC, 1/4A 250 VDC<br>4A 125 VAC "L" | ONE PLACE (.0)                               | ±.030                 |
| DIFFERENTIAL TRAVEL — — .050 MAX |                                                                                           | TWO PLACE (.00)                              | ±.015                 |
| OVERTRAVEL — — — .080 MIN        |                                                                                           | THREE PLACE (.000)                           | ±.005                 |
| RELEASE TRAVEL — — — .013 MIN    |                                                                                           | ANGLES                                       | ±                     |
|                                  |                                                                                           | WEIGHT                                       |                       |

