




**Part Number :** [639023100](#)

**Product Description :** FineAdjust Applicator for  
2.50mm Pitch Crimp Terminal

**Series Number :** 207127

**Status :** Active

**Product Category :** Applicators and Crimp Modules



---

## Documents and Resources

### Tooling Specifications

[ATS-639023100-001.pdf](#)

[TM-638000029-001.pdf](#)

[TM-638000029DE-001.pdf](#)

[TM-638000029SP-001.pdf](#)

[TM-638000029FR-001.pdf](#)

[TM-638000029IT-001.pdf](#)

[TM-638000029JP-001.pdf](#)

[TM-638000029KR-001.pdf](#)

[TM-638000029MY-001.pdf](#)

[TM-638000029PL-001.pdf](#)

[TM-638000029RU-001.pdf](#)

[TM-638000029SK-001.pdf](#)

[TM-638000029TH-001.pdf](#)

[TM-638000029VN-001.pdf](#)

[TM-638000029CN-001.pdf](#)

[TM-638000029TW-001.pdf](#)

[TM-638004900-001.pdf](#)

[TM-638004900CN-001.pdf](#)

[TM-638004900SP-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for 2.50mm Pitch Crimp Terminal
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust

Tool Type	Applicator
UPC	884982476134
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

## Physical

Net Weight	5001.683/g
------------	------------

## Mates With / Use With

### Use with Part(s)

Description	Part Number
TM-2000 Universal Press	<a href="#"><u>638008300</u></a>
TM-2000 Universal Press (Europe 220V)	<a href="#"><u>638008400</u></a>
TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10 AWG	<a href="#"><u>638017200</u></a>
TM-3000 Universal Crimp Press, 220AC 50/60Hz, Used for product up to 10 AWG	<a href="#"><u>638017300</u></a>
TM-4000 Universal Crimp Press, 240AC 50/60Hz, Used for product up to 4 AWG	<a href="#"><u>638017600</u></a>

Use With	Most Industry Standard Presses or Wire Process Machines
----------	--

---

## Applicable Parts

Description	Part Number
2.50mm Pitch, Mini-SPOX Female Crimp Terminal, 28-22 AWG, Reel	<u>08701039</u>
2.50mm Pitch Mini-SPOX Wire-to-Board Crimp Terminal, 28-22 AWG, for 5264Housing, Spring Box, Pre-Tin Plating, Low Profile Version	<u>39000160</u>

---

This document was generated on May 21, 2026