


C3225C0G2E153J200AA

Applications	 Commercial Grade
	 Please refer to Part No. CGA6M3C0G2E153J200AA for automotive use.
Feature	Mid Mid Voltage (100 to 630V)
Series	C3225 [EIA CC1210]



Size	
Length(L)	3.20mm +/-0.40mm
Width(W)	2.50mm +/-0.30mm
Thickness(T)	2.00mm +/-0.20mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	


Electrical Characteristics	
Capacitance	15nF +/-5%
Rated Voltage	250Vdc
Temperature Characteristic	C0G(0+/-30ppm/degC)
Q	1000 Min.
Insulation Resistance	10000M Min.

Other	
Soldering Method	Reflow
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	1000 Pcs Min.


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

C3225C0G2E153J200AA


Characteristic Graphs




C3225C0G2E153J200AA




C3225C0G2E153J200AA




C3225C0G2E153J200AA



C3225C0G2E153J200AA



C3225C0G2E153J200AA(DC Bias = 0V) C3225C0G2E153J200AA(DC Bias = 125V)



•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.