

Product data sheet

Specifications



APC NetShelter Switched Rack PDU, 0U, 20A, 100-120V, 24 NEMA 5-20R outlets

AP8930

Overview

Presentation

APC Switched Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and active monitoring. Remote outlet level controls allow power on/off functionality for power recycling to remotely reboot equipment and restrict unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and low profile circuit breakers. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched Rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.

Lead time

Usually in Stock

Main

Colour	Black
Product or component type	PDU
PDU type	Switched
Cord length	3.00 m
Number of cables	1
Provided equipment	Installation guide Rack mounting brackets Serial configuration cable Safety guide

Complementary

Input Voltage	120 V
Height	179.1 cm
Width	5.5 cm
Output Voltage	120 V
Depth	4.6 cm
Product weight	6.52 kg
Mounting location	Side
Mounting preference	No preference
Input Plug Type	NEMA L5-20P
Mounting mode	Rack-mounted
Rack units	0U

Mounting position	Vertical
[In] rated current	16 A
Permissible voltage	100...120 V
Input current limits	20 A
Load capacity	1920 VA
Network frequency	50/60 Hz
Outlet type and quantity	24 NEMA 5-20R

Environment

Product certifications	cUL listed UL listed
Standards	FCC part 15 class A ICES-003 UL 60950-1
Ambient air temperature for operation	-5...60 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0...15240 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	200.6 cm
Package 1 Width	10.83 cm
Package 1 Length	16.47 cm
Package 1 Weight	8.6 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	2623
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
REACH Regulation	REACH Declaration
Halogen-free status	Product contains halogen above thresholds

Energy efficiency

Energy Efficiency Optimized	Energy efficient product
-----------------------------	---------------------------------

Use Again

Repack and remanufacture

End of life manual availability	End of Life Information
Removable battery	Yes
Take-back	No