



Part Number : 1000570156

Product Description : Temp-Flex High-Performance Flat-Ribbon Cable, 16 Circuits, 1.00mm Pitch, 28 AWG, Silver Plated Copper, UL 20424, 7/36 Stranded Extruded FEP, Blue with Blue Polarity Stripe



Series Number : 100057

Status : Active

Product Category : Specialty Wire and Cable

Engineering Number : F2807S-16-0394-55

Documents & Resources

Drawings

[1000570156_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Specialty Wire and Cable
Series	100057
Description	Temp-Flex High-Performance Flat-Ribbon Cable, 16 Circuits, 1.00mm Pitch, 28 AWG, Silver Plated Copper, UL 20424, 7/36 Stranded Extruded FEP, Blue with Blue Polarity Stripe
Product Name	Temp-Flex
UPC	889056600828

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	300V AC

Physical

Cable Length	100 ft/spool, 10 ft min length, 2 lengths/spool max
Circuits (Loaded)	16
Color - Cable Jacket	Blue w/Blue Polarity Stripe
Insulation	FEP
Material - Outer Jacket	FEP
Material - Plating Mating	Silver
Net Weight	17.072/g
Packaging Type	Spool

Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-55° to +200°C
Wire/Cable Type	7/36 Stranded, High-Performance Flat-Ribbon, UL 20424
Wire Size (AWG)	28

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Molex Picoflex

This document was generated on Sep 29, 2025