


HONEYWELL PART NUMBER
21SM369
PRODUCT CODE TXL9903

REV	DOCUMENT	CHANGED BY	CHECK
2	0038111	PK 20MAY08	ASD



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø.087 MAX ON .375 ±.002 CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

RELEASE NO.	PR - 24456
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 		DRAWN	VK	18 OCT 07	Honeywell			
OPERATING FORCE — — — 3 OZ MAX		CONTACT ARRANGEMENT SPDT					CHECK	RJ	18 OCT 07				
RELEASE FORCE— — — — 1 OZ MIN		30 VOLTS DC RATING			0.030 0.015 0.005		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC			
DIFFERENTIAL TRAVEL— — — .002 MAX			SEA LEVEL	50,000 FT									
OVERTRAVEL — — — — — .005 MIN		MAXIMUM INRUSH 24 AMP					INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME	REV
		INDUCTIVE	3 AMP	2.5 AMP						B	I	21SM369	2
		RESISTIVE			5 AMP	5 AMP	RASTER			SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1
		APPROVALS			KEMA, CE	5A, 250V ~ T85 1E4  				UL, CSA	5A, 250 VAC  	BRAND L4	