


1200V thinQ!™ SiC Schottky Diode

Features:

- Revolutionary Semiconductor Material - Silicon Carbide
- Switching Behaviour Benchmark
- No Reverse Recovery / No Forward Recovery
- Temperature Independent Switching Behaviour
- Qualified According to JEDEC¹⁾ Based on Target Applications

Applications:

- Motor Drives / Solar Inverters
- High Voltage CCM PFC
- Switch Mode Power Supplies
- High Voltage Multipliers



Chip Type	V _{BR}	I _F	Die Size	Package
IDC08S120	1200V	7.5A	2.012 x 2.012 mm ²	sawn on foil

MECHANICAL PARAMETERS

Raster size	2.012 x 2.012	mm ²
Anode pad size	1.476 x 1.476	
Area total / active	4.05 / 3	
Thickness	362	μm
Wafer size	75	mm
Flat position	0	deg
Max. possible chips per wafer	901 pcs	
Passivation frontside	Photoimide	
Pad metal	3200 nm Al	
Backside metal	1400 nm Ni Ag –system suitable for epoxy and soft solder die bonding	
Die bond	Electrically conductive glue or solder	
Wire bond	Al, ≤ 350μm	
Reject ink dot size	Ø ≥ 0.3 mm	
Recommended storage environment	Store in original container, in dry nitrogen, < 6 month at an ambient temperature of 23°C	

ELECTRICAL PARAMETERS

Maximum Ratings

Parameter	Symbol	Condition	Value	Unit
Repetitive peak reverse voltage	V_{RRM}	$T_j = 25^\circ\text{C}$	1200	V
DC blocking voltage	V_{DC}		1200	
Continuous forward current, limited by T_{jmax}	I_F		7.5	A
Surge non repetitive forward current, sine halfwave	$I_{F,SM}$	$T_C = 25^\circ\text{C}, t_P = 10\text{ ms}$	39	
		$T_C = 150^\circ\text{C}, t_P = 10\text{ ms}$	33	
Repetitive peak forward current, limited by thermal resistance R_{th}	$I_{F,RM}$	$T_C = 100^\circ\text{C}, T_j = 150^\circ\text{C}, D = 0.1$	32	
Non-repetitive peak forward current	$I_{F,max}$	$T_C = 25^\circ\text{C}, t_P = 10\mu\text{s}$	160	A^2s
i^2t value	$\int i^2 dt$	$T_C = 25^\circ\text{C}, t_P = 10\text{ ms}$	7	
		$T_C = 150^\circ\text{C}, t_P = 10\text{ ms}$	5	
Operating junction and storage temperature range	T_j, T_{stg}		-55...+175	$^\circ\text{C}$

Static Characteristics (tested on wafer)

Parameter	Symbol	Conditions	Value			Unit
			min.	Typ.	max.	
Reverse current	I_R	$V_R = 1200\text{V}, T_j = 25^\circ\text{C}$		8	180	μA
Diode forward voltage	V_F	$I_F = 7.5\text{A}, T_j = 25^\circ\text{C}$		1.6	1.8	V

Static Characteristics (not subject to production test - verified by design / characterization)

Parameter	Symbol	Conditions	Value			Unit
			min.	Typ.	max.	
Reverse current	I_R	$V_R = 1200\text{V}, T_j = 150^\circ\text{C}$		30	1000	μA
Diode forward voltage	V_F	$I_F = 7.5\text{A}, T_j = 150^\circ\text{C}$		2.5	3	V

Dynamic Characteristics (not subject to production test - verified by design / characterization)


Parameter	Symbol	Conditions		Value			Unit
				min.	Typ.	max.	
Total capacitive charge ³⁾	Q_C	$I_F \leq I_{F,max}$ $di/dt = 200 A/ms$ $V_R = 1200 V$	$T_J = 150\text{ }^{\circ}C$		27		nC
Switching time ²⁾	t_c		$T_J = 150\text{ }^{\circ}C$			<10	ns
Total capacitance	C	$f = 1 MHz$	$V_R = 1 V$		380		pF
			$V_R = 300 V$		30		
			$V_R = 600 V$		27		

¹⁾ J-STD20 and JESD22

²⁾ t_c is the time constant for the capacitive displacement current waveform (independent from T_J , I_{LOAD} and di/dt), different from t_{rr} , which is dependent on T_J , I_{LOAD} , di/dt . No reverse recovery time constant t_{rr} due to absence of minority carrier inject.

³⁾ Only capacitive charge occurring, guaranteed by design (independent from T_J , I_{LOAD} and di/dt).

CHIP DRAWING





IDC08S120

FURTHER ELECTRICAL CHARACTERISTICS

This chip data sheet refers to the device data sheet

INFINEON TECHNOLOGIES

IDH08S120

Description:

AQL 0,65 for visual inspection according to failure catalogue

Electrostatic Discharge Sensitive Device according to MIL-STD 883

Test-Normen Villach/Prüffeld

Published by
Infineon Technologies AG
81726 Munich, Germany
© Infineon Technologies AG 2007
All Rights Reserved

Attention please!

The information herein is given to describe certain components and shall not be considered as warranted characteristics.

Terms of delivery and rights to technical change reserved.

We hereby disclaim any and all warranties, including but not limited to warranties of non-infringement, regarding circuits, descriptions and charts stated herein.

Infineon Technologies is an approved CECC manufacturer.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office in Germany or our Infineon Technologies Representatives world-wide (see address list).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and / or maintain and sustain and / or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.