


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PROPOSAL DESIGN	03AUG2018	WY	SZ
	A	REVISED	27JUL2020	WY	SZ









1. "TE", PART NUMBER, AND DATECODE TO BE MARKED IN AREA SHOWN. PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.
2. MATERIAL:
   HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC,BLACK, UL94 V-O
   SIGNAL CONTACT - COPPER ALLOY
   POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
3. CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA OF POWER AND SIGNAL CONTACTS.
4. MECHANICAL CONNECTOR KEEP OUT ZONE.
5. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
6. PCB - HOLE DIAMETERS ARE FINISHED HOLE SIZE.
7. PCB - .0453±.0010 DRILLLED HOLES PLATED WITH .0003 MIN Sn OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 ±.003 HOLE.

5LP + 24S + 2P	2334570-4
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±0.25
3 PLC	±0.15
4 PLC	±-
ANGLES	±-

MATERIAL - 2

FINISH - 3

DWN	WY	03AUG2018
CHK	WY	03AUG2018
APVD	SZ	03AUG2018
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	

TE Connectivity

NAME RIGHT ANGLE RECEPTACLE, SOLDER MULTI-BEAM PLUS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2334570-4	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 2 | REV A

1470-19 (3/13)


Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

PART NUMBER	ROWS		POWER P2	POWER P2	POWER P1	POWER P1	SIGNAL 6	SIGNAL 5	SIGNAL 4	SIGNAL 3	SIGNAL 2	SIGNAL 1	LOW POWER LP5	LP4	LP3	LP2	LP1	
2334570-4	E	HD	RN	RM	RN	RM	V4	V4	V4	V4	V4	V4	LM	LM	LM	LM	LM	HD
	D						V3	V3	V3	V3	V3	V3						
	C						V2	V2	V2	V2	V2	V2						
	B						V1	V1	V1	V1	V1	V1						
5LP + 24S + 2P																		



RECOMMENDED PCB LAYOUT

STD SOLDER LOW POWER CONTACT	LM
STD SOLDER TYPE SIGNAL CONTACT,R/A,ROW D	V4
STD SOLDER TYPE SIGNAL CONTACT,R/A,ROW C	V3
STD SOLDER TYPE SIGNAL CONTACT,R/A,ROW B	V2
STD SOLDER TYPE SIGNAL CONTACT,R/A,ROW A	V1
STD SOLDER POWER CONTACT,RIGHT	RN
STD SOLDER POWER CONTACT,LEFT	RM
HOUSING	HOUSING
HOLD DOWN, MULTI-BEAM	HD
DESCRIPTION	IDENTIFIER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±0.25
3 PLC ±0.15
4 PLC ±-
ANGLES ±-

MATERIAL - 2

FINISH - 3

DWN WY 03AUG2018
CHK WY 03AUG2018
APVD SZ 03AUG2018
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME RIGHT ANGLE RECEPTACLE, SOLDER MULTI-BEAM PLUS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2334570-4	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 2 OF 2 | REV A

1470-19 (3/13)

Downloaded from Arrow.com.