

1404548

https://www.phoenixcontact.com/us/products/1404548

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Control cabinet feed-through, M12, 8-pos., X-coded to RJ45 socket, socket input 90°, IP65/67

Your advantages

· Compact design

Commercial data

| Item number | 1404548 |
|--------------------------------------|---------------------|
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB18 |
| Product key | ABNPBC |
| Catalog page | Page 348 (C-2-2019) |
| GTIN | 4046356699419 |
| Weight per piece (including packing) | 37 g |
| Weight per piece (excluding packing) | 36 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |



1404548

https://www.phoenixcontact.com/us/products/1404548

Technical data

Product properties

| Туре | M12 |
|---------------------|---------------|
| Product type | Female insert |
| Sensor type | Ethernet |
| Number of positions | 8 |
| Connection profile | M12 |
| Number of slots | 1 |
| Shielded | yes |
| Cable outlet | angled |
| Thread type | M12 |

Insulation characteristics

| Overvoltage category | III |
|----------------------|-----|
| Degree of pollution | 2 |

Electrical properties

| Maximum load current | 0.5 A |
|---|-------------------|
| Rated voltage (III/3) | 72 V (DC) |
| Rated surge voltage | 0.8 kV |
| Rated current | 1.75 A |
| Nominal voltage U _N | 48 V |
| Nominal current I _N | 0.5 A |
| Transmission medium | Copper |
| Transmission characteristics (category) | CAT6 _A |
| Power transmission | PoE++ |

Connection data

Connection technology

| Connection method | Coupling |
|-------------------|----------|
|-------------------|----------|

Material specifications

| Color | black |
|--|--------------|
| Flammability rating according to UL 94 | V0 |
| Material of grip body | PA |
| Contact material | Copper alloy |
| Housing material | Plastic |

Connector

Connection 1

| Туре | Socket M12 |
|--------------|------------------|
| Locking type | Screw connection |



1404548

https://www.phoenixcontact.com/us/products/1404548

| Coding type | X | |
|--|--------------|--|
| Shielded | yes | |
| Insertion/withdrawal cycles | ≥ 750 (RJ45) | |
| Degree of protection | IP65/IP67 | |
| Connection 2 | | |
| Туре | Socket RJ45 | |
| Degree of protection | IP20 | |
| Mechanical properties Mechanical data | | |
| Insertion/withdrawal cycles | ≥ 100 | |
| Environmental and real-life conditions Ambient conditions | | |
| Degree of protection | IP65 | |
| | | |

Mounting

Ambient temperature (operation)

Ambient temperature (storage/transport)

| Mounting type | Rear mounting |
|---------------|------------------|
| g type | . tour mountaing |

IP65/IP67, when installed

-25 °C ... 85 °C

-25 °C ... 85 °C





1404548

https://www.phoenixcontact.com/us/products/1404548

Drawings

Dimensional drawing






Pin assignment of M12 female, 8-pos., X-coded, view: female side



1404548

https://www.phoenixcontact.com/us/products/1404548

Schematic diagram




RJ45 socket insert




1404548

https://www.phoenixcontact.com/us/products/1404548



Dimensional drawing




Mounting cutout



1404548

https://www.phoenixcontact.com/us/products/1404548





Exploded drawing



1404548

https://www.phoenixcontact.com/us/products/1404548

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1404548

| UL Listed Approval ID: E335024-20140306 | | | | | |
|--|--|--------------------------------|--------------------------------|-------------------|-------------------------------|
| | | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | | 60 V | 0.5 A | - | - |

| cUL Listed Approval ID: E335024-20140306 | | | | | |
|--|--|--------------------------------|--------------------------------|-------------------|-------------------------------|
| | | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | | 60 V | 0.5 A | - | - |

cULus Listed



1404548

https://www.phoenixcontact.com/us/products/1404548

Classifications

ECLASS

| | ECLASS-11.0 | 27440312 | | |
|----|-------------|----------|--|--|
| | ECLASS-13.0 | 27440312 | | |
| | ECLASS-12.0 | 27440312 | | |
| ET | ETIM | | | |
| | ETIM 9.0 | EC002641 | | |
| | | | | |

UNSPSC

| UNSPSC 21.0 | 39121400 |
|-------------|----------|
|-------------|----------|



1404548

https://www.phoenixcontact.com/us/products/1404548

Environmental product compliance

| REACh SVHC | Lead 7439-92-1 |
|------------|--|
| | |
| China RoHS | Environmentally Friendly Use Period = 50 years |
| | For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads" |

Phoenix Contact 2024 © - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com