

Data sheet

RP025xxHBWC Typ 107

Page 1/6

P/N

311071xx

xx=number of poles


2019/10/24

Version: Q

Illustrations



Dimensional drawing



See enlarged drawings at the end of document

Product specification

- screw type terminal block, pluggable
- centerline 5.00 mm, direction of connection 90°
- wire protector, fittable without loss of poles
- color black
- Wire entry perpendicular to plug direction

Data sheet

RP025xxHBWC Typ 107

Page 2/6

P/N
311071xx

xx=number of poles

2019/10/24

Version: Q

Technical Data

General Data

Tightening torque SEV	0.5 Nm		
Tightening torque UL	6 lb-in		
min. number of poles	2		
max. number of poles	24		
Insulating material class	CTI 600		
clearance/creepage dist.	2.3 mm		
protection category	IP00		
Min. insul. strip length	6 mm		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	100 V	320 V	320 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV

Connection Data

rat.wiring solid AWGmax	0.08 mm ² - 2.5 mm ² / AWG 28 - AWG 12
rat.wiring strand.AWGmax	0.08 mm ² - 2.5 mm ² / AWG 28 - AWG 12

Approvals

 V / A / AWG	300 / 10 / 28 - 12
approval UL - File No.	E121004
 2.5 mm ²	250 V / 2.5 kV / 10 A

Material

insulating material	PA66
flammability class	V0
contact material	CuSn
contact surface	Sn
terminal body material	CuZn
terminal body surface	Ni
screw surface	Zn Cr(VI)-frei/free
wire protector material	CuSn
wire protector surface	Sn
screw thread	M3
Glow-Wire Flammability GWFI	960 °C acc. to IEC 60695-2-12
Glow-Wire Flammability GWIT	775 °C acc. to IEC 60695-2-13

Data sheet
RP025xxHBWC Typ 107

Page 3/6

P/N
311071xx

xx=number of poles

2019/10/24

Version: Q

Technical Data

REACH - substance (SVHC) Lead / 7439-92-1

Climatic Data

upper limit temperature 105 °C

lower limit temperature -40 °C

General

Tolerance ISO 2768 -mH



Data sheet RP025xxHBWC Typ 107

Page 4/6

P/N
311071xx

xx=number of poles

2019/10/24

Version: Q

Accessories

P/N	Designation
710084	710084
710085	710085
710121-2	710121
710122-2	710122
716846	716846

U | Contact

Data sheet RP025xxHBWC Typ 107

Page 5/6

P/N
311071xx

xx=number of poles

2019/10/24


Version: Q

Counterpart

P/N	Designation
310171	PR015xxVBHC Typ 017
310271	PR015xxVBVC Typ 027
310391	PT055xxHBHC Typ 039
310411	PT065xxVBEN Typ 041
310421	PT065xxVBVN Type 042
314171	PM035xxVBHC Typ 417

Illustrations

Dimensional drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 5 \text{ mm } [0.197]$