






DIMENSION

Dim A	(N-1)X5.08+6.58
Dim B	(N-1)X5.08

N = Number of poles

Poles	Tolerance
2p-6p	±0.15
7p-12p	±0.20
13p-18p	±0.30
19p-24p	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	2010.01.15	Add cULus standard	Jacke
△	2010.08.24	The design is changed	Jacke
△	2010.08.24	The design is changed	Jacke
△	07/10`12	Change the material of contact from Brass to Copper	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item① Terminal(housing):Thermoplastic (UL94V-0)
- Item② Terminal (Cover):Thermoplastic (UL94V-0)
- Item③ Terminal screw:Steel Zinc plating "- " slot type
- Item④ Clamp:Brass(CuZn) Ni plating
- Item⑤ Male contact Pin: Copper, Tin plated

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 4Lb-In
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus
- Critical dimension: ∇

V8 xx 51 x 0 xxxx G

G RoHS compliant
(lead<4%)
In copper Alloy

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V8 5.08 Series W/O flange				
PART NO.	V8xx51x0xxxxG			DWG NO.	8V80301	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Chen Bo 07/10`12	Chen Bo 07/10`12		Tolerance	
					UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV.: E	X.XX ±0.10
						X° ±1°